




L1007.160

BALL & NEEDLE CAGES

Material

Ball steel (100Cr6 to DIN 5401, class 3),
ball cage plastic (PA 12).

Can also be supplied with corrosion resistant stainless balls (AISI 304) balls,
plastic balls (POM) or ceramic balls.

Order No.	d ₁	p ₁	h ₁	l ₁	w ₁	d ₂	No. of rollers
L1007.160-0100	16	20	20	100	3.5	16.2	5
L1007.160-0200	16	20	20	200	3.5	16.2	9
L1007.160-0300	16	20	20	300	3.5	16.2	14
L1007.160-0400	16	20	20	400	3.5	16.2	19
L1007.160-0500	16	20	20	500	3.5	16.2	24
L1007.160-0600	16	20	20	600	3.5	16.2	29
L1007.160-0700	16	20	20	700	3.5	16.2	34
L1007.160-0800	16	20	20	800	3.5	16.2	39
L1007.160-0900	16	20	20	900	3.5	16.2	44
L1007.160-1000	16	20	20	1000	3.5	16.2	49