




Linear Cage - Crossed Roller steel cage

Ball & Needle
Cages



L1008.015-AA

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, class 3, hardened to 60 HRC) retaining cage steel.

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.015-AA-0100	1.5	3	3.75	100	0.2	32	1600
L1008.015-AA-0200	1.5	3	3.75	200	0.2	66	3300
L1008.015-AA-0300	1.5	3	3.75	300	0.2	99	4950
L1008.015-AA-0400	1.5	3	3.75	400	0.2	132	6600
L1008.015-AA-0500	1.5	3	3.75	500	0.2	166	8300
L1008.015-AA-0600	1.5	3	3.75	600	0.2	199	9950
L1008.015-AA-0700	1.5	3	3.75	700	0.2	232	11600
L1008.015-AA-0800	1.5	3	3.75	800	0.2	265	13250
L1008.015-AA-0900	1.5	3	3.75	900	0.2	299	14950
L1008.015-AA-1000	1.5	3	3.75	1000	0.2	332	16600