




Linear Cage - Crossed Roller steel cage

Ball & Needle
Cages



L1008.090-AA

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, class 3, hardened to 60 HRC) retaining cage steel.

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.090-AA-0100	9	18	20.5	100	1	7	5922
L1008.090-AA-0200	9	18	20.5	200	1	14	13144
L1008.090-AA-0300	9	18	20.5	300	1	21	20367
L1008.090-AA-0400	9	18	20.5	400	1	28	27589
L1008.090-AA-0500	9	18	20.5	500	1	27	34811
L1008.090-AA-0600	9	18	20.5	600	1	32	42033
L1008.090-AA-0700	9	18	20.5	700	1	38	49256
L1008.090-AA-0800	9	18	20.5	800	1	43	56478
L1008.090-AA-0900	9	18	20.5	900	1	49	63700
L1008.090-AA-1000	9	18	20.5	1000	1	55	70922