




Linear Cage - Crossed Roller steel cage

Ball & Needle
Cages



L1008.120-AA

BALL & NEEDLE CAGES

Material

Steel rollers (100Cr6, class 3, hardened to 60 HRC) retaining cage steel.

Important Notes

For load ratings calculations the maximum recommended load is 1/3 of the max. static

load.

Order No.	d_1	p_1	h_1	l_1	w_1	No. of rollers	Dyn. load C N max.
L1008.120-AA-0100	12	22	26.5	100	1.2	4	8864
L1008.120-AA-0200	12	22	26.5	200	1.2	8	20227
L1008.120-AA-0300	12	22	26.5	300	1.2	13	31591
L1008.120-AA-0400	12	22	26.5	400	1.2	17	42955
L1008.120-AA-0500	12	22	26.5	500	1.2	22	54318
L1008.120-AA-0600	12	22	26.5	600	1.2	26	65682
L1008.120-AA-0700	12	22	26.5	700	1.2	31	77045
L1008.120-AA-0800	12	22	26.5	800	1.2	35	88409
L1008.120-AA-0900	12	22	26.5	900	1.2	40	99730
L1008.120-AA-1000	12	22	26.5	1000	1.2	44	111136