





Linear Cage - Needle Roller

Ball & Needle Cages



L1009.040

BALL & NEEDLE CAGES

Material

Needle roller, steel (100Cr6 to DIN5401, grade 28, class 3), retaining cage plastic

(PA 12).

Order No.	d_1	l_2	p_1	h_1	l_1	w_1	No. of rollers
L1009.040-0100	4	23.8	7	30	100	3	14
L1009.040-0200	4	23.8	7	30	200	3	28
L1009.040-0300	4	23.8	7	30	300	3	42
L1009.040-0400	4	23.8	7	30	400	3	56
L1009.040-0500	4	23.8	7	30	500	3	70
L1009.040-0600	4	23.8	7	30	600	3	84
L1009.040-0700	4	23.8	7	30	700	3	98
L1009.040-0800	4	23.8	7	30	800	3	112
L1009.040-0900	4	23.8	7	30	900	3	126
L1009.040-1000	4	23.8	7	30	1000	3	141