





Linear Cage - Needle Roller

Ball & Needle Cages



L1009.052

BALL & NEEDLE CAGES

Material

Needle roller, steel (100Cr6 to DIN5401, grade 28, class 3), retaining cage plastic

(PA 12).

Order No.	d_1	l_2	p_1	h_1	l_1	w_1	No. of rollers
L1009.052-0100	5	27.8	9	35	100	3.5	11
L1009.052-0200	5	27.8	9	35	200	3.5	22
L1009.052-0300	5	27.8	9	35	300	3.5	33
L1009.052-0400	5	27.8	9	35	400	3.5	44
L1009.052-0500	5	27.8	9	35	500	3.5	55
L1009.052-0600	5	27.8	9	35	600	3.5	66
L1009.052-0700	5	27.8	9	35	700	3.5	77
L1009.052-0800	5	27.8	9	35	800	3.5	88
L1009.052-0900	5	27.8	9	35	900	3.5	99
L1009.052-1000	5	27.8	9	35	1000	3.5	110