
Linear Shaft



## **Ø20 Hardened Stainless Shafts** for linear bearings





L1772.20

### Material

Corrosion resistant stainless steel (440C, DIN 1.4112, X90 CrMo18) hardened. Surface hardness 53-56 HRC, Rht 450Hv2. Surface finish 0.3-0.6µ Ra, ground and polished to 8-12 cla.

Yield stress: >420 N/mm<sup>2</sup>.

Tensile strength: >785 N/mm<sup>2</sup>.

#### **Technical Notes**

Suitable for use with linear bearings. Tolerance, h6 standard, special tolerances on request. Straightness 0,2mm/m.

## **Tips**

Modifications, drilled and tapped holes, retainer grooves, special coatings etc. are

Shaft lengths are cut to typically ± 2mm, ends are not hardened.

Order No.	d <sub>1</sub>	$I_1$	Depth of hardness	Weight
	tol. h6	_	min.	kg
L1772.20-0100	20	100	0.9	0.247
L1772.20-0150	20	150	0.9	0.371
L1772.20-0200	20	200	0.9	0.494
L1772.20-0250	20	250	0.9	0.618
L1772.20-0300	20	300	0.9	0.741
L1772.20-0350	20	350	0.9	0.865
L1772.20-0400	20	400	0.9	0.988
L1772.20-0450	20	450	0.9	1.112
L1772.20-0500	20	500	0.9	1.235
L1772.20-0550	20	550	0.9	1.359
L1772.20-0600	20	600	0.9	1.482
L1772.20-0650	20	650	0.9	1.606
L1772.20-0700	20	700	0.9	1.729
L1772.20-0750	20	750	0.9	1.853
L1772.20-0800	20	800	0.9	1.976
L1772.20-0850	20	850	0.9	2.100
L1772.20-0900	20	900	0.9	2.223
L1772.20-0950	20	950	0.9	2.347
L1772.20-1000	20	1000	0.9	2.470
L1772.20-1050	20	1050	0.9	2.594
L1772.20-1100	20	1100	0.9	2.717
L1772.20-1150	20	1150	0.9	2.841
L1772.20-1200	20	1200	0.9	2.964
L1772.20-1250	20	1250	0.9	3.088
L1772.20-1300	20	1300	0.9	3.211
L1772.20-1350	20	1350	0.9	3.335
L1772.20-1400	20	1400	0.9	3.458
L1772.20-1450	20	1450	0.9	3.582
L1772.20-1500	20	1500	0.9	3.705
L1772.20-1550	20	1550	0.9	3.829
L1772.20-1600	20	1600	0.9	3.952

0333 207 4498



## Linear Shaft Bars

## **Ø20 Hardened Stainless Shafts**

for linear bearings



Order No.	d <sub>1</sub> tol. h6	$I_1$	Depth of hardness	Weight
14550004050		1650	min.	kg
L1772.20-1650	20	1650	0.9	4.076
L1772.20-1700	20	1700	0.9	4.199
L1772.20-1750 L1772.20-1800	20 20	1750 1800	0.9 0.9	4.323 4.446
L1772.20-1850	20	1850	0.9	4.446
L1772.20-1850 L1772.20-1900	20	1900	0.9	4.693
L1772.20-1900 L1772.20-1950	20	1950	0.9	4.817
L1772.20-2000	20	2000	0.9	4.940
L1772.20-2050	20	2050	0.9	5.064
L1772.20-2100	20	2100	0.9	5.187
L1772.20-2150	20	2150	0.9	5.311
L1772.20-2200	20	2200	0.9	5.434
L1772.20-2250	20	2200	0.9	5.558
L1772.20-2300	20	2300	0.9	5.681
L1772.20-2350	20	2350	0.9	5.805
L1772.20-2400	20	2400	0.9	5.928
L1772.20-2450	20	2450	0.9	6.052
L1772.20-2500	20	2500	0.9	6.175
L1772.20-2550	20	2550	0.9	6.299
L1772.20-2600	20	2600	0.9	6.422
L1772.20-2650	20	2650	0.9	6.546
L1772.20-2700	20	2700	0.9	6.669
L1772.20-2750	20	2750	0.9	6.793
L1772.20-2800	20	2800	0.9	6.916
L1772.20-2850	20	2850	0.9	7.040
L1772.20-2900 L1772.20-2950	20	2900	0.9	7.163
	20	2950 3000	0.9 0.9	7.287 7.410
L1772.20-3000 L1772.20-3050	20 20	3050	0.9	7.534
L1772.20-3030	20	3100	0.9	7.657
L1772.20-3150	20	3150	0.9	7.781
L1772.20-3130	20	3200	0.9	7.904
L1772.20-3250	20	3250	0.9	8.028
L1772.20-3300	20	3300	0.9	8.151
L1772.20-3350	20	3350	0.9	8.275
L1772.20-3400	20	3400	0.9	8.398
L1772.20-3450	20	3450	0.9	8.522
L1772.20-3500	20	3500	0.9	8.645
L1772.20-3550	20	3550	0.9	8.769
L1772.20-3600	20	3600	0.9	8.892
L1772.20-3650	20	3650	0.9	9.016
L1772.20-3700	20	3700	0.9	9.139
L1772.20-3750	20	3750	0.9	9.263
L1772.20-3800	20	3800	0.9	9.386
L1772.20-3850	20	3850	0.9	9.510
L1772.20-3900	20	3900	0.9	9.633
L1772.20-3950 L1772.20-4000	20 20	3950 4000	0.9 0.9	9.757 9.880
L1772.20-4000 L1772.20-4050	20	4000	0.9	9.880
L1772.20-4050 L1772.20-4100	20	4100	0.9	10.127
L1772.20-4150	20	4150	0.9	10.127
L1772.20-4130	20	4200	0.9	10.231
L1772.20-4250	20	4250	0.9	10.498
L1772.20-4300	20	4300	0.9	10.621
L1772.20-4350	20	4350	0.9	10.745
L1772.20-4400	20	4400	0.9	10.868
L1772.20-4450	20	4450	0.9	10.992
L1772.20-4500	20	4500	0.9	11.115
L1772.20-4550	20	4550	0.9	11.239
L1772.20-4600	20	4600	0.9	11.362
L1772.20-4650	20	4650	0.9	11.486
L1772.20-4700	20	4700	0.9	11.609
L1772.20-4750	20	4750	0.9	11.733
L1772.20-4800	20	4800	0.9	11.856
L1772.20-4850	20	4850	0.9	11.980
L1772.20-4900	20	4900	0.9	12.103
L1772.20-4950	20	4950	0.9	12.227
L1772.20-5000	20	5000	0.9	12.350



# **Ø20 Hardened Stainless Shafts**

for linear bearings



Order No.	$d_1$	I <sub>1</sub>	Depth of hardness	Weight
	tol. ĥ6	*	min.	kg
L1772.20-5050	20	5050	0.9	12.474
L1772.20-5100	20	5100	0.9	12.597
L1772.20-5150	20	5150	0.9	12.721
L1772.20-5200	20	5200	0.9	12.844
L1772.20-5250	20	5250	0.9	12.968
L1772.20-5300	20	5300	0.9	13.091
L1772.20-5350	20	5350	0.9	13.215
L1772.20-5400	20	5400	0.9	13.338
L1772.20-5450	20	5450	0.9	13.462
L1772.20-5500	20	5500	0.9	13.585
L1772.20-5550	20	5550	0.9	13.709
L1772.20-5600	20	5600	0.9	13.832
L1772.20-5650	20	5650	0.9	13.956
L1772.20-5700	20	5700	0.9	14.079
L1772.20-5750	20	5750	0.9	14.203
L1772.20-5800	20	5800	0.9	14.326
L1772.20-5850	20	5850	0.9	14.450
L1772.20-5900	20	5900	0.9	14.573
L1772.20-5950	20	5950	0.9	14.697
L1772.20-6000	20	6000	0.9	14.820



## **Technical Information**

Linear shaft bars



## Hardened steel linear shafting (L1770 - L1771)

Carbon steel to BS 070M55 hardened to 60-65 HRC. Carbon Steel B.S. 070M55 is a medium carbon steel which is used when greater strength and hardness is desired than in it's as rolled condition. Extreme size accuracy, straightness and concentricity are combined to minimise wear in high speed applications. Suitable for use with all types of linear bushings.

### Corrosion resistant steel (L1772)

440C is a high carbon chromium martensitic stainless steel, generally supplied in the annealed condition with a maximum hardness of 50-55 HR<sub>c</sub>. Characterised by good corrosion resistance in mild domestic and industrial environments, including fresh water, organic materials, mild acids, various petroleum products, coupled with extreme high strength, hardness and wear resistance when in the hardened and tempered condition. Used for parts requiring a combination of excellent wear resistance, plus reasonable corrosion resistance. Typical applications are: ball bearings and races, bushings, cutlery, chisels, knife blades, pump parts, surgical instruments, valve seats etc. Material magnetic in all conditions. Suitable for use with all types of linear bushings.

#### Stainless steel AISI 303 (L1773)

303 is a free machining chromium-nickel austenitic stainless steel with good strength and good corrosion resistance, as supplied in the annealed condition. Characterised by excellent machinability and non galling properties due to its higher sulphur content, which has the effect of slightly lowering its corrosion resistance. It is however, fairly resistant to general atmospheric corrosion, general foodstuffs, sterilizing solutions, dyestuffs, most organic chemicals, plus some inorganic chemicals. But has very limited resistance to acids. 303 cannot be hardened by thermal treatment, but strength and hardness can be increased substantially by cold working, with subsequent reduction in ductility. It is used primarily for production runs involving extensive machining, or complex parts requiring excellent machinability. Typical uses are: architectural components, food processing equipment, dairy equipment, dying industry, hardware and kitchenware manufacturing and allied industries. Commonly used to manufacture bolts and nuts, bushes, gears, shafts, valve bodies and fittings etc. Material is non magnetic in the annealed condition, but can become mildly magnetic following heavy cold working. Annealing is required to rectify if necessary.

Not suitable for use with linear ball bushings, please use ceramic bearings.

### Stainless steel AISI 303 (L1774)

316 is a chromium-nickel-molybdenum austenitic stainless steel with good strength and excellent corrosion resistance, as supplied in the annealed condition. Characterised by high corrosion resistance in marine and industrial atmospheres, it exhibits excellent resistance to chloride attack and against complex sulphur compounds employed in the pulp and paper processing industries. The addition of 2% to 3% of molybdenum increases its resistance to pitting corrosion and improves its creep resistance at elevated temperatures. Also it displays good oxidation resistance at elevated temperatures and has excellent weldability. AISI 316 cannot be hardened by thermal treatment, but strength and hardness can be increased substantially by cold working, with subsequent reduction in ductility. It is used extensively by the marine, chemical, petrochemical, pulp and paper, textile, transport, manufacturing and allied industries. Typical uses are: architectural components, textile equipment, pulp and paper processing equipment, marine equipment and fittings, photographic equipment and x-ray equipment etc. Material non magnetic in the annealed condition, but can become mildly magnetic following heavy cold working. Annealing is required to rectify if necessary.

Note: Optimum corrosion resistance is achieved in the annealed condition. Not suitable for use with linear ball bushings; please use ceramic bearings.



## **Linear Shafts**

**Overview** 

# L1770 - Hardened steel shafts L1771 - Hardened hollow shafts For use with linear bearings. For use with linear bearings. Hollowed for lighter weight. Ø12 to Ø50 Ø6 to Ø60 L1772 - Hardened Stainless shafts L1773 - Stainless 303 shafts For use with linear bearings Soft stainless, high anti-corrosion. Anti-corrosion. Not for use with ball bush linear bearings. Ø6 to Ø60 Ø6 to Ø60 L1774 - Stainless 316 shafts L1778 - Aluminium shafts Soft stainless, very high anti-corrosion. Light weight, non-magnetic. Not for use with ball bushing linear bearings. Ø10 to Ø50 Ø6 to Ø60



ov-linear-shafts-overview-rnh - Updated - 28-02-2023