



**L1009.100**

BALL & NEEDLE CAGES

**Material** (PA 12).

Needle roller, steel (100Cr6 to DIN5401, grade 28, class 3), retaining cage plastic

Order No.	$d_1$	$l_2$	$p_1$	$h_1$	$l_1$	$w_1$	No. of rollers
L1009.100-0100	10	10	13	16	100	2.5	7
L1009.100-0200	10	10	13	16	200	2.5	15
L1009.100-0300	10	10	13	16	300	2.5	22
L1009.100-0400	10	10	13	16	400	2.5	30
L1009.100-0500	10	10	13	16	500	2.5	38
L1009.100-0600	10	10	13	16	600	2.5	45
L1009.100-0700	10	10	13	16	700	2.5	53
L1009.100-0800	10	10	13	16	800	2.5	60
L1009.100-0900	10	10	13	16	900	2.5	68
L1009.100-1000	10	10	13	16	1000	2.5	76