





Linear Cage - Needle Roller

Ball & Needle Cages



L1009.160

BALL & NEEDLE CAGES

Material

Needle roller, steel (100Cr6 to DIN5401, grade 28, class 3), retaining cage plastic

(PA 12).

Order No.	d ₁	l ₂	p ₁	h ₁	l ₁	w ₁	No. of rollers
L1009.160-0100	16	16	22	28	100	4	4
L1009.160-0200	16	16	22	28	200	4	8
L1009.160-0300	16	16	22	28	300	4	13
L1009.160-0400	16	16	22	28	400	4	17
L1009.160-0500	16	16	22	28	500	4	22
L1009.160-0600	16	16	22	28	600	4	26
L1009.160-0700	16	16	22	28	700	4	30
L1009.160-0800	16	16	22	28	800	4	35
L1009.160-0900	16	16	22	28	900	4	39
L1009.160-1000	16	16	22	28	1000	4	44