





Flanged Carriages - Standard blackened

Linear Guide-
ways



L1016.F-BC

LINEAR GUIDEWAYS

Material

Hardened and ground steel. Matt black oxide ceramic layer, Thickness 2-10 μ . No deformation of the parts. Resistant to acids, alkalis and solvents. Relatively soft layer (up to 350 HV), which clears away by rolling over in the area of the raceways. Suitable for applications in the optic and

medical industry.

Technical Notes

Select the size and number of carriages to suit the required load then select the required rail length, (see part nos. L1016.15 through to L1016.55). Standard preload carriages are K_0 (no

preload) or K_1 (0,02 x dynamic load capacity). Other preloads available on request.

Tips

Improved version with ball cages allowing the carriages to be removed from the rail without the balls falling out.

Order No.	Rail size	l_1	h_1	l_2	w_1	l_3	h_2	h_3	h_4	d_1	h_5	d_2	h_6	w_2	w_3	w_4	l_4	Weight kg
L1016.F15-BC	15	58.6	24	40.2	47	30	3.3	8.0	13.0	M 5	6.0	4.5	5.5	38	15	16.0	5.0	0.21
L1016.F15-L-BC	15	66.1	24	47.7	47	30	3.3	8.0	13.0	M 5	6.0	4.5	5.5	38	15	16.0	5.0	0.23
L1016.F20-BC	20	69.3	30	48.5	63	40	4.5	9.0	16.3	M 6	8.5	6.0	7.1	53	20	21.5	15.6	0.40
L1016.F20-L-BC	20	82.1	30	61.3	63	40	4.5	9.0	16.3	M 6	8.5	6.0	7.1	53	20	21.5	15.6	0.46
L1016.F25-BC	25	79.2	36	57.5	70	45	5.8	10.0	19.2	M 8	9.0	7.0	10.2	57	23	23.5	15.6	0.57
L1016.F25-L-BC	25	93.9	36	72.2	70	45	5.8	10.0	19.2	M 8	9.0	7.0	10.2	57	23	23.5	15.6	0.72

Order No.	l_5	d_3	d_4	M_x Nm	M_y Nm	M_z Nm	Dyn. load $C_{rad \& ax}$ kN	Static load $C_{0rad \& ax}$ kN
L1016.F15-BC	60	7.5	M3 x 0,5	137	120	120	11.67	19.90
L1016.F15-L-BC	60	7.5	M3 x 0,5	166	171	171	14.12	24.05
L1016.F20-BC	60	9.5	M6 x 1,0	289	224	224	17.98	30.96
L1016.F20-L-BC	60	9.5	M6 x 1,0	376	366	366	23.30	40.11
L1016.F25-BC	60	11.0	M6 x 1,0	447	358	358	25.25	41.73
L1016.F25-L-BC	60	11.0	M6 x 1,0	576	577	577	32.44	53.63