




35mm Needle Roller Linear Rail

heavy duty

Linear Guide-ways



L1017.35

LINEAR GUIDEWAYS

Material

Hardened and ground steel (typically 60 HRC).

Technical Notes

For carriages to suit the required load see

part nos. L1017.FN (flanged) and L1017.UN (unflanged).
Supplied with plastic covers for screws.

Tips

These are very heavy duty needle roller

rails and can only be used with corresponding needle roller carriages L1017. For standard linear guideways and carriages see part no. L1016.

Order No.	Rail size	w ₁	h ₁	l ₁	l ₂	For screws	h ₂	d ₁	d ₂	l ₃	Weight kg
L1017.35-0320	30	34	32	320	40	M8	17	9	15	20	18.4
L1017.35-0400	30	34	32	400	40	M8	17	9	15	20	23.0
L1017.35-0480	30	34	32	480	40	M8	17	9	15	20	27.6
L1017.35-0560	30	34	32	560	40	M8	17	9	15	20	32.1
L1017.35-0640	30	34	32	640	40	M8	17	9	15	20	36.7
L1017.35-0720	30	34	32	720	40	M8	17	9	15	20	41.3
L1017.35-0800	30	34	32	800	40	M8	17	9	15	20	45.9
L1017.35-0880	30	34	32	880	40	M8	17	9	15	20	50.5
L1017.35-0960	30	34	32	960	40	M8	17	9	15	20	55.1
L1017.35-1040	30	34	32	1040	40	M8	17	9	15	20	2.3
L1017.35-1120	30	34	32	1120	40	M8	17	9	15	20	6.9
L1017.35-1200	30	34	32	1200	40	M8	17	9	15	20	11.5
L1017.35-1280	30	34	32	1280	40	M8	17	9	15	20	16.1
L1017.35-1360	30	34	32	1360	40	M8	17	9	15	20	20.7
L1017.35-1440	30	34	32	1440	40	M8	17	9	15	20	25.3
L1017.35-1520	30	34	32	1520	40	M8	17	9	15	20	29.8
L1017.35-1600	30	34	32	1600	40	M8	17	9	15	20	34.4
L1017.35-1680	30	34	32	1680	40	M8	17	9	15	20	39.0
L1017.35-1760	30	34	32	1760	40	M8	17	9	15	20	43.6
L1017.35-1840	30	34	32	1840	40	M8	17	9	15	20	48.2
L1017.35-1920	30	34	32	1920	40	M8	17	9	15	20	52.8
L1017.35-2000	30	34	32	2000	40	M8	17	9	15	20	0.0
L1017.35-2080	30	34	32	2080	40	M8	17	9	15	20	4.6
L1017.35-2160	30	34	32	2160	40	M8	17	9	15	20	9.2
L1017.35-2240	30	34	32	2240	40	M8	17	9	15	20	13.8
L1017.35-2320	30	34	32	2320	40	M8	17	9	15	20	18.4
L1017.35-2400	30	34	32	2400	40	M8	17	9	15	20	23.0
L1017.35-2480	30	34	32	2480	40	M8	17	9	15	20	27.6
L1017.35-2560	30	34	32	2560	40	M8	17	9	15	20	32.1
L1017.35-2640	30	34	32	2640	40	M8	17	9	15	20	36.7
L1017.35-2720	30	34	32	2720	40	M8	17	9	15	20	41.3
L1017.35-2800	30	34	32	2800	40	M8	17	9	15	20	45.9



Order No.	Rail size	w ₁	h ₁	l ₁	l ₂	For screws	h ₂	d ₁	d ₂	l ₃	Weight kg
L1017.35-2880	30	34	32	2880	40	M8	17	9	15	20	50.5
L1017.35-2960	30	34	32	2960	40	M8	17	9	15	20	55.1
L1017.35-3040	30	34	32	3040	40	M8	17	9	15	20	2.3
L1017.35-3120	30	34	32	3120	40	M8	17	9	15	20	6.9
L1017.35-3200	30	34	32	3200	40	M8	17	9	15	20	11.5
L1017.35-3280	30	34	32	3280	40	M8	17	9	15	20	16.1
L1017.35-3360	30	34	32	3360	40	M8	17	9	15	20	20.7
L1017.35-3440	30	34	32	3440	40	M8	17	9	15	20	25.3
L1017.35-3520	30	34	32	3520	40	M8	17	9	15	20	29.8
L1017.35-3600	30	34	32	3600	40	M8	17	9	15	20	34.4
L1017.35-3680	30	34	32	3680	40	M8	17	9	15	20	39.0
L1017.35-3760	30	34	32	3760	40	M8	17	9	15	20	43.6
L1017.35-3840	30	34	32	3840	40	M8	17	9	15	20	48.2
L1017.35-3920	30	34	32	3920	40	M8	17	9	15	20	52.8
L1017.35-4000	30	34	32	4000	40	M8	17	9	15	20	229.6