




55mm Needle Roller Linear Rail

heavy duty

Linear Guide-ways



L1017.55

LINEAR GUIDEWAYS

Material

Hardened and ground steel (typically 60 HRC).

Technical Notes

For carriages to suit the required load see


part nos. L1017.FN (flanged) and L1017.UN (unflanged).
Supplied with plastic covers for screws.

Tips

These are very heavy duty needle roller

rails and can only be used with corresponding needle roller carriages L1017. For standard linear guideways and carriages see part no. L1016.

Order No.	Rail size	w ₁	h ₁	l ₁	l ₂	For screws	h ₂	d ₁	d ₂	l ₃	Weight kg
L1017.55-0315	55	53	48	315	60	M14	20	16	24	29	4.79
L1017.55-0420	55	53	48	420	60	M14	20	16	24	29	6.38
L1017.55-0525	55	53	48	525	60	M14	20	16	24	29	7.98
L1017.55-0630	55	53	48	630	60	M14	20	16	24	29	9.58
L1017.55-0735	55	53	48	735	60	M14	20	16	24	29	11.17
L1017.55-0840	55	53	48	840	60	M14	20	16	24	29	12.77
L1017.55-0945	55	53	48	945	60	M14	20	16	24	29	14.36
L1017.55-0960	55	53	48	960	60	M14	20	16	24	29	14.59
L1017.55-1050	55	53	48	1050	60	M14	20	16	24	29	15.96
L1017.55-1155	55	53	48	1155	60	M14	20	16	24	29	17.56
L1017.55-1260	55	53	48	1260	60	M14	20	16	24	29	19.15
L1017.55-1365	55	53	48	1365	60	M14	20	16	24	29	20.75
L1017.55-1470	55	53	48	1470	60	M14	20	16	24	29	22.34
L1017.55-1575	55	53	48	1575	60	M14	20	16	24	29	23.94
L1017.55-1680	55	53	48	1680	60	M14	20	16	24	29	25.54
L1017.55-1785	55	53	48	1785	60	M14	20	16	24	29	27.13
L1017.55-1890	55	53	48	1890	60	M14	20	16	24	29	28.73
L1017.55-1995	55	53	48	1995	60	M14	20	16	24	29	30.32
L1017.55-2100	55	53	48	2100	60	M14	20	16	24	29	31.92
L1017.55-2205	55	53	48	2205	60	M14	20	16	24	29	33.52
L1017.55-2310	55	53	48	2310	60	M14	20	16	24	29	35.11
L1017.55-2415	55	53	48	2415	60	M14	20	16	24	29	36.71
L1017.55-2520	55	53	48	2520	60	M14	20	16	24	29	38.30
L1017.55-2625	55	53	48	2625	60	M14	20	16	24	29	39.90
L1017.55-2730	55	53	48	2730	60	M14	20	16	24	29	41.50
L1017.55-2835	55	53	48	2835	60	M14	20	16	24	29	43.09
L1017.55-2940	55	53	48	2940	60	M14	20	16	24	29	44.69
L1017.55-3045	55	53	48	3045	60	M14	20	16	24	29	46.28
L1017.55-3150	55	53	48	3150	60	M14	20	16	24	29	47.88
L1017.55-3255	55	53	48	3255	60	M14	20	16	24	29	49.48
L1017.55-3360	55	53	48	3360	60	M14	20	16	24	29	51.07
L1017.55-3465	55	53	48	3465	60	M14	20	16	24	29	52.67



Order No.	Rail size	w ₁	h ₁	l ₁	l ₂	For screws	h ₂	d ₁	d ₂	l ₃	Weight kg
L1017.55-3570	55	53	48	3570	60	M14	20	16	24	29	54.26
L1017.55-3675	55	53	48	3675	60	M14	20	16	24	29	55.86
L1017.55-3780	55	53	48	3780	60	M14	20	16	24	29	57.46
L1017.55-3885	55	53	48	3885	60	M14	20	16	24	29	59.05
L1017.55-3990	55	53	48	3990	60	M14	20	16	24	29	60.65