




Low Profile Crossed Roller Table

aluminium/steel

Linear Tables



L1027.AL

LINEAR TABLES

Material

Aluminium body, black anodised carriage.
Hardened chrome steel crossed roller rail set.

Positional repeatability: 3µ.

Coefficient of friction: 0,003 typical.

Technical Notes

Straight line accuracy: 3µ/25mm of travel.

Tips


Stroke is centred on the mid-point of the slides (ie 50% of total stroke each way).


Order No.	Stroke l_1	Load kg max.	$w_1 \pm 0.1$	l_2	$h_1 \pm 0.1$	h_2	w_2	d_1	No. of carr holes	l_3	l_4	w_3
L1027.020-012-AL	12	23	20	25	8	4	6.6	M2	4	3.5	1x18	14
L1027.020-018-AL	18	32	20	35	8	4	6.6	M2	4	3.5	1x28	14
L1027.020-025-AL	25	47	20	45	8	4	6.6	M2	4	12.5	1x20	14
L1027.020-032-AL	32	54	20	55	8	4	6.6	M2	4	12.5	1x30	14
L1027.020-040-AL	40	60	20	65	8	4	6.6	M2	6	12.5	2x20	14
L1027.020-045-AL	45	73	20	75	8	4	6.6	M2	4	22.5	1x30	14
L1027.020-050-AL	50	79	20	85	8	4	6.6	M2	6	12.5	2x30	14
L1027.030-018-AL	18	40	30	35	12	6	12.0	M4	4	3.5	1x28	22
L1027.030-030-AL	30	63	30	50	12	6	12.0	M4	4	3.5	1x43	22
L1027.030-040-AL	40	75	30	65	12	6	12.0	M4	4	17.5	1x30	22
L1027.030-050-AL	50	95	30	80	12	6	12.0	M4	4	17.5	1x45	22
L1027.030-060-AL	60	105	30	95	12	6	12.0	M4	6	17.5	2x30	22
L1027.030-070-AL	70	120	30	110	12	6	12.0	M4	4	32.5	1x45	22
L1027.030-080-AL	80	130	30	125	12	6	12.0	M4	6	17.5	2x45	22
L1027.040-030-AL	30	126	40	55	16	8	16.0	M5	4	7.5	1x40	30
L1027.040-045-AL	45	183	40	80	16	8	16.0	M5	4	7.5	1x65	30
L1027.040-060-AL	60	220	40	105	16	8	16.0	M5	4	27.5	1x50	30
L1027.040-075-AL	75	275	40	130	16	8	16.0	M5	4	27.5	1x75	30
L1027.040-090-AL	90	310	40	155	16	8	16.0	M5	6	27.5	2x50	30
L1027.040-105-AL	105	355	40	180	16	8	16.0	M5	4	52.5	1x75	30
L1027.040-130-AL	130	375	40	205	16	8	16.0	M5	6	27.5	2x75	30

Order No.	l_5	No. of base holes	h_3	l_6	h_4	l_7	d_2	d_3	Moment M_x Nm max.	Moment M_y Nm max.	Moment M_z Nm max.
L1027.020-012-AL	3.5	2	3.5	18	2.5	-	3.9	2.6	0.80	1.29	1.33
L1027.020-018-AL	5.0	2	3.5	25	2.5	-	3.9	2.6	1.04	2.59	2.71
L1027.020-025-AL	3.5	4	3.5	38	2.5	25	3.9	2.6	1.51	4.55	4.79
L1027.020-032-AL	3.5	4	3.5	48	2.5	29	3.9	2.6	1.74	5.36	5.63
L1027.020-040-AL	5.0	4	3.5	55	2.5	31	3.9	2.6	1.94	8.16	8.33



Order No.	l ₅	No. of base holes	h ₃	l ₆	h ₄	l ₇	d ₂	d ₃	Moment M _x	Moment M _y	Moment M _z
									Nm max.	Nm max.	Nm max.
L1027.020-045-AL	5.0	4	3.5	65	2.5	35	3.9	2.6	2.27	11.5	12.1
L1027.020-050-AL	5.0	4	3.5	75	2.5	40	3.9	2.6	2.55	13.9	14.6
L1027.030-018-AL	5.0	2	5.5	25	3.8	-	6.1	4	2.35	3.06	3.21
L1027.030-030-AL	7.5	2	5.5	35	3.8	-	6.1	4	3.71	6.49	6.80
L1027.030-040-AL	5.0	4	5.5	55	3.8	33	6.1	4	4.41	9.92	10.4
L1027.030-050-AL	5.0	4	5.5	70	3.8	40	6.1	4	5.58	15.3	16.1
L1027.030-060-AL	5.0	4	5.5	85	3.8	45	6.1	4	6.17	20.0	21.0
L1027.030-070-AL	7.5	4	5.5	95	3.8	50	6.1	4	7.05	26.4	27.7
L1027.030-080-AL	7.5	4	5.5	110	3.8	55	6.1	4	7.64	32.4	34.1
L1027.040-030-AL	7.5	2	7.5	40	5.2	-	8.3	5.2	9.87	14.8	15.5
L1027.040-045-AL	6.0	4	7.5	68	5.2	43	8.3	5.2	14.4	31.0	32.6
L1027.040-060-AL	7.5	4	7.5	90	5.2	55	8.3	5.2	17.2	48.5	50.9
L1027.040-075-AL	7.5	4	7.5	115	5.2	65	8.3	5.2	21.5	74.7	78.4
L1027.040-090-AL	7.5	4	7.5	140	5.2	95	8.3	5.2	24.2	100	105
L1027.040-105-AL	7.5	4	7.5	165	5.2	85	8.3	5.2	27.8	136	142
L1027.040-130-AL	7.5	4	7.5	190	5.2	90	8.3	5.2	29.4	158	166





Size + Weight

For light/medium loads

L1020-L1037

Ball roller versions



L1024 - L1038

Cross roller versions



L1020 - L1026

Stainless steel versions




L1022 - L1023

For heavy duty loads and motorised

L3000-L3500

Needle roller & dovetail stage



L3170 - L3194

Motorised stages



L3500 - L3510

Micrometer driven stages




L3100 - L3123



Factors affecting stage selections...

- Size and weight of load
- Moment loads
- Stroke required
- Accuracy required
- Usage conditions of water, chemicals, shock loads etc.




Generally ball slides are less expensive but cross roller slides can carry 8 to 10 times the load of ball slides.

The stroke is centred on the mid point of the slides (i.e. 50% of the stroke each way).

A selection...

L1020 Crossed roller tables	L1022/23 Cross roller table	L1024 Ball slide tables
 <p>Steel and aluminium, accuracy typically 5µ.</p>	 <p>Stainless Steel, accuracy typically 3µ.</p>	 <p>Aluminium, accuracy typically 12µ.</p>
L1026 Crossed roller slide tables	L1028 Precision ball slide tables	L1029 Precision crossed roller tables
 <p>Aluminium, accuracy typically 5µ.</p>	 <p>Aluminium, accuracy typically 3µ.</p>	 <p>Aluminium, accuracy typically 3µ.</p>
L1034 Flanged ball slide tables - precision	L1038 Anti-creep ball slide tables	L1039 Non-magnetic ball slide
 <p>With flange accuracy to 1µ.</p>	 <p>Special anti-creep function prevents cage misalignment.</p>	 <p>Non-magnetic accuracy typically 3µ.</p>



Steel - L1020

- Standard steel / cast iron




Aluminium - L1021

- Lower weight, lower profile
- Good for high accelerations



Stainless steel - L1022 + L1023



- Stainless steel (440C+Ni) corrosion resistant



Rated life

$$L \text{ (Km)} = \left(\frac{F_t \cdot C}{F_w \cdot P_c} \right)^{3.33} \times 100$$

- F_t = temperature factor
- F_w = load factor
- C = basic dynamic load (kN) see tables
- P_c = radial load (kN)



Height tolerance:

- Height $\pm 100\mu$
- Motorised parts $\pm 10\mu$
- Strokes from 10 to 950mm
- Loads to 48kN

Load factor F_w

Shock	Speed	F_w
None	Very slow	1.0 - 1.2
Small	Slow	1.2 - 1.5



Technical accuracy measurements

- High accuracy.
- Low friction: virtually frictionless. Providing stable performance at lower high speeds.
- Rigid: incorporating cross roller linear rails to provide high load capacity as well as high moment load capacity.
- Installation: easy to install with pre-drilled holes in carriage and base. Ensure mounting surface faces are accurately machined.

LINEAR TABLES

Table accuracy (μ)			Rail accuracy (μ)		
Table length	Carriage top parallelism	Carriage side parallelism	N tolerance	M tolerance	Straightness
0-50	2	4	-15 -35	-30 -70	2
50-100	2	5			2
100-150	3	6			3
150-200	3	7			3
200-250	3	7			3
250-300	3	7			3
300-350	4	8			4
350-400	4	8			4
400-450	4	8			4
450-500	4	8			4
500-550	4	9			4
550-600	4	9			4

