



L1900.CPNX

LONG LINEAR RAILS

Material

Stainless steel rollers with 2RS seals (splashproof). Lubricated for life

Technical Notes

To choose the correct replacement roller select either the concentric or eccentric

roller with the correct seal type.

Order No.	For rail type	For rail size	Seal type	Roller type	C N	C _{Grad} N	d ₁	d ₂	d ₃	w ₁	w ₂	w ₃	w ₄	w ₅
L1918.CPNX18-2RS	T and U	18	Rubber	Concentric	765	410	14.0	M4	6	4.0	5.5	1.55	1.8	-
L1918.CPAX18-2RS	T and U	18	Rubber	Eccentric	765	410	14.0	M4	6	4.0	5.5	1.55	1.8	0.4
L1928.CPNX28-2RS	T and U	28	Rubber	Concentric	2130	1085	23.2	M5	10	7.0	7.0	2.20	3.8	-
L1928.CPAX28-2RS	T and U	28	Rubber	Eccentric	2130	1085	23.2	M5	10	7.0	7.0	2.20	3.8	0.6
L1935.CPNX35-2RS	T and U	35	Rubber	Concentric	4020	1755	28.2	M5	12	7.5	9.0	2.55	4.2	-
L1935.CPAX35-2RS	T and U	35	Rubber	Eccentric	4020	1755	28.2	M5	12	7.5	9.0	2.55	4.2	0.7
L1943.CPNX43-2RS	T and U	43	Rubber	Concentric	6140	2750	35.0	M6	12	11	12.0	2.50	4.5	-
L1943.CPAX43-2RS	T and U	43	Rubber	Eccentric	6140	2750	35.0	M6	12	11	12.0	2.50	4.5	0.8