





Stainless Micrometer XY Stages

front drive

Manual Positioning Stages



L3121

MANUAL POSITIONING STAGES

Material

Stainless steel (440C) with electroless nickel plating.

Technical Notes

Straightness accuracy 5μ.

Spring loaded micrometer allows precise repeatable adjustments with low friction and zero backlash.

Micrometer increments 0,01mm.


Important Notes

Stroke is centred on the mid-point of the slides (ie 50% of total stroke each way).

3D CAD available.

Order No.	Travel	d ₁	d ₂	d ₃ tol. H7	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄	h ₅
L3121.040	13	M3	-	4	13	10	32.0	35.0	29.0	26.5	13.0
L3121.060	13	M4	M3	4	13	10	32.0	35.0	29.0	26.5	13.0
L3121.080	25	M4	M3	4	13	10	40.0	44.3	36.8	34.5	16.8
L3121.100	25	M4	M4	4	13	10	40.0	44.3	36.8	34.5	16.8


Order No.	h ₆	l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	l ₇	w ₁	w ₂	w ₃	Load kg max.
L3121.040	10.5	40	98.5	58.5	16	32	15.5	32	26	20.5	21	9.7
L3121.060	10.5	60	118.5	58.5	25	50	16.5	50	36	20.5	20	19.6
L3121.080	14.5	80	160	80.0	25	70	24.5	70	55	24.5	24	26.1
L3121.100	14.5	100	180	80.0	25	90	24.5	90	67.5	24.5	24	33.6



There are two different load ratings for these stages.

Ball slides:


These have precision steel balls rolling in the tracks. They are the least expensive, loads up to 28Kg.



Locking options


Posi-lock:

Allows locking of the carriage in place with a friction locking mechanism.




Cross roller slides:

These have the same dimensions but have rollers allowing the slide to carry large loads and absorb greater moment loads up to 54Kg.



Locking micrometer:


Locking of the micrometer to fix the micrometer setting.



Front drive micrometer positioning stages



X Stage




XY Stage




XYZ Stage


Side drive micrometer positioning stages



X Stage



XY Stage



XYZ Stage

Also available in stainless steel.