




Dovetail Stages - Rack & Pinion

long stroke, X axis

Manual Positioning Stages



L3305

MANUAL POSITIONING STAGES

Material

Aluminium body blackened, steel knob.

Technical Notes

Travel 18mm for one revolution.

Minimum vernier reading 0,1mm.

Straightness accuracy 30μ.

Use screwdriver to adjust knob to allow coarse or fine adjustment.

Order No.	h_1	Travel	Load kg max.	w_1	Accuracy	d_1	d_2	d_3 for
L3305.100	25	±40	3.0	25	30μ	M2	M2	M3
L3305.150	25	±60	3.0	25	40μ	M4	M2	M3
L3305.200	25	±95	3.0	25	50μ	M4	M2	M3

Order No.	d_4	d_5	h_2	h_3	h_4	l_1	l_2	l_3	l_4	l_5	w_2	w_3	w_4
L3305.100	15	8	17.1	14.8	6	100	42	30	25	15	15	40.2	24.5
L3305.150	15	8	17.1	14.8	6	150	42	30	25	15	15	40.2	24.5
L3305.200	15	8	17.1	14.8	6	200	42	30	25	15	15	40.2	24.5