




Medium Duty Sliders - Size 28

no side seal - front fixing - with wiper



Long Linear
Rails



L1928.CS

LONG LINEAR RAILS

Material

Zinc plated steel body.
Steel rollers (100Cr6) with metal (2Z) or rubber (2RS) seals.

Select the relevant carriage for the rail and the required number of carriages to carry the load (taking into account any moment loads).

Unlike the N series sliders these CS sliders do not have protective side seals.

The 3 and 5 bearing sliders can be used either way up in the rail dependent on where the loads will be applied. Easy to install (one or more rollers are eccentric allowing for adjustable preload). Coefficient of friction (without seals) 0.003.

Quiet and fast (up to 5 m/s).

Technical Notes

To be used with compact rail size 28.

Tips

The U rail sliders cannot accept axial loads.

Order No.	For rail type	No. of rollers	Seal type	d ₁	$\begin{matrix} h_1 \\ +0.25 - \\ 0.10 \end{matrix}$	$\begin{matrix} h_2 \\ +0.0 - \\ 0.10 \end{matrix}$	$\begin{matrix} h_3 \\ +0.05 - \\ 0.35 \end{matrix}$	l ₁	l ₂	l ₃	l ₄	M _x Nm	M _y Nm	Weight g
L1928.28CS-080-2RST	T	3	Rubber	M5	28	14.9	21.7	80	100	35	22.5	6.2	16	0.15
L1928.28CS-080-2RSU	U	3	Rubber	M5	28	14.9	21.7	80	100	35	22.5	0	0	0.15
L1928.28CS-100-2RSTA	T	4	Rubber	M5	28	14.9	21.7	100	120	50	25	11.5	21.7	0.19
L1928.28CS-100-2RSUA	U	4	Rubber	M5	28	14.9	21.7	100	120	50	25	0	0	0.19
L1928.28CS-100-2RSTB	T	4	Rubber	M5	28	14.9	21.7	100	120	50	25	11.5	21.7	0.19
L1928.28CS-100-2RSUB	U	4	Rubber	M5	28	14.9	21.7	100	120	50	25	0	0	0.19
L1928.28CS-125-2RST	T	5	Rubber	M5	28	14.9	21.7	125	145	25	25	11.5	29	0.24
L1928.28CS-125-2RSU	U	5	Rubber	M5	28	14.9	21.7	125	145	25	25	0	0	0.24
L1928.28CS-150-2RSTA	T	6	Rubber	M5	28	14.9	21.7	150	170	50	25	13.7	36.2	0.29
L1928.28CS-150-2RSUA	U	6	Rubber	M5	28	14.9	21.7	150	170	50	25	0	0	0.29
L1928.28CS-150-2RSTB	T	6	Rubber	M5	28	14.9	21.7	150	170	50	25	13.7	36.2	0.29
L1928.28CS-150-2RSUB	U	6	Rubber	M5	28	14.9	21.7	150	170	50	25	0	0	0.29



Automotion
AN ESSENTA COMPANY

0333 207 4498

sales@automotioncomponents.co.uk




Order No.	M _{zr} Nm	M _{zl} Nm	w ₁ ±0.15	w ₂	Dyn. load C N max.	Static load C _{0 ax.} N max.	Arrangement type	Static load C _{0 rad.} N max.
L1928.28CS-080-2RST	27.2	27.2	23.9	9.7	4260	640	-	2170
L1928.28CS-080-2RSU	27.2	27.2	23.9	9.7	4260	0	-	2170
L1928.28CS-100-2RSTA	27.2	81.7	23.9	9.7	4260	750	A	2170
L1928.28CS-100-2RSUA	27.2	81.7	23.9	9.7	4260	0	A	2170
L1928.28CS-100-2RSTB	81.7	27.2	23.9	9.7	4260	750	B	2170
L1928.28CS-100-2RSUB	81.7	27.2	23.9	9.7	4260	0	B	2170
L1928.28CS-125-2RST	81.7	81.7	23.9	9.7	5065	900	-	2580
L1928.28CS-125-2RSU	81.7	81.7	23.9	9.7	5065	0	-	2580
L1928.28CS-150-2RSTA	81.7	136.1	23.9	9.7	5065	1070	A	2580
L1928.28CS-150-2RSUA	81.7	136.1	23.9	9.7	5065	0	A	2580
L1928.28CS-150-2RSTB	136.1	81.7	23.9	9.7	5065	1070	B	2580
L1928.28CS-150-2RSUB	136.1	87.1	23.9	9.7	5065	0	B	2580



Compact Rails

Introduction



Compact Rail

The compact rail systems are unique. They have many major advantages over other rail systems.

Easy and cost-effective to set up


The rails are easy to set up and can adjust for some misalignment of the structure on which it is being used. The compact rail system achieves this by using a master (T type) rail, and a slave (U type) rail. This allows the sliders in the T rail to remain fixed in place but allows lateral movement of the sliders in the U rail to adapt to any misalignment and avoid any issues of stiction.

Slave (U) rails have flat, parallel raceways that allow free lateral movement of the sliders. This flexibility can mean a large saving in the machining of the structure surface making it a very cost-effective solution.



Fast, smooth and quiet

The unique eccentric roller allows easy preload adjustment for smooth running. Very high speeds allowed, very quiet operation.



Anti-corrosion option


Alloy coating or nickel plating of the rails and sliders can be applied to provide a corrosion resistant solution.

Dirt and debris resistant

The internal raceways are resistant to dirt and debris, larger roller bearings with seals and wipers are used (compared to small ball bearings on other systems).

Unlimited rail lengths

Rails can be easily joined together for unlimited rail lengths, and extra hole needs to be machined at the joint area. The rails need to be selected so they are “matched” and a joining tool needs to be used to align the rails.





Specifications

- Maximum speed 9 m/s.
- Maximum acceleration 20 m/s².
- Maximum unjoined rail length 3600 mm.
- 4 rail sizes – 18, 28, 35 and 43.
- Three rail types – T rail, U rail and K rail.
- Rail lengths from 160mm upwards.
- Rail raceways hardened and ground.
- Accuracy 0,15mm over 3,5 metres.
- Maximum radial load per slider is 15,000 N.
- Temperature range -30°C to +120°C.
- Roller bearings seals either 2Z (dust proof) or 2RS (splash proof), lubricated for life.
- Roller bearings from 100Cr6.
- Easy adjustment of preload.
- Three slider body types.
- Rails can be joined together, please contact our Technical Department for details.
- Special anti-corrosion coatings and finishes on request.

Applications



Special purpose & packaging machines

Precision positioning systems
handling units
robotic systems • cutting machines




Seating

Sliding seats
disability ramps
seat extensions



Safety guarding

Extending protective systems
sliding gates
automatic pick & place



Sliding doors & windows

Internal sliding doors
gates • roof lights
display cases



Photography & lighting

Sliding tracks
positioning of lights
shielding systems



Medical technology

X-ray equipment
dental chairs
bed extensions



Food, drink & pharmaceuticals

Food handling conveyors
pharmaceutical factories
stainless display equipment



Transport (naval)

Sliding hatches
pull-out storage



Transport (rail)

Seat adjustment
sliding doors
battery removal units




Transport (automotive)

Ambulance sliding systems
fire fighting vehicles
sliding panels




Transport (military)


Sliding seats
protective hatches
stretcher extensions




Rail sizes



Rail types



Sliders




Compact Rail from Automotion Components



Orientation of rails


The radial load that the sliders can take is significantly higher than the axial load, so where possible the rails should be set up with the sliders taking the loads in this plane.



One of the key benefits of the compact rail system is that it compensates for misalignment in the structure. This often results in a major cost saving when compared to the use of other guideways which have to be very accurately installed.

The compact rail system achieves this by using a master (T type) rail, and a slave (U type) rail. This allows the slides in the T rail to remain fixed in place but allows lateral movement of the sliders in the U rail to adapt to any misalignment and avoid any issues of stiction.

U rails have flat, parallel raceways that allow free lateral movement of the sliders. The maximum lateral movement for each size is shown in later tables.



Using flat rails

It is acceptable (but not the preferred method), to use rails as below but the alignment accuracy needed is slightly greater and in this set-up only T type rails can be used.

In this case the axial load figure C_{0ax} should be used in any calculations (which is considerably less than the radial load figure C_{0rad}).

