




Captive Screws - Pan Head

TX drive - 316 stainless



Captive Screws



P0150.A4

MADE IN BRITAIN

CAPTIVE SCREWS

Material

Stainless steel (AISI 316, 1.440). Tensile strength 480 N/mm². Proof stress min. 200 N/mm², austenitic stainless steel. Also available on request in steel (anodised, black oxide or zinc plated), stainless steel (AISI 303, 1.4305), brass, aluminium etc.

tive 2006/42/EC. Generally to ISO 14583. Often used with our captive washers (P0168) or retaining flanges (P0169 - for sheet metal applications). The use of our captive washers should be considered when fitted in panels with unthreaded holes.

reduced diameter shank and should not be tightened to the recommended torque for an equivalent machine screw of size d₁.

*M 8 sizes have a reduced TX size.

Technical Notes

Used to comply with the Machinery Direc-

Important Notes

Please note that these screws have a

Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	d ₃ max.	d ₄ min.	h ₁ max.	l ₂ ±0.25	TX size
P0150.030-008-A4	M 3	8	2.0	6	3.5	2.5	4.5	TX-10
P0150.030-010-A4	M 3	10	2.0	6	3.5	2.5	4.5	TX-10
P0150.030-016-A4	M 3	16	2.0	6	3.5	2.5	4.5	TX-10
P0150.030-020-A4	M 3	20	2.0	6	3.5	2.5	4.5	TX-10
P0150.030-025-A4	M 3	25	2.0	6	3.5	2.5	4.5	TX-10
P0150.030-030-A4	M 3	30	2.0	6	3.5	2.5	4.5	TX-10
P0150.040-008-A4	M 4	8	2.8	8	4.5	3.2	6.0	TX-20
P0150.040-010-A4	M 4	10	2.8	8	4.5	3.2	6.0	TX-20
P0150.040-012-A4	M 4	12	2.8	8	4.5	3.2	6.0	TX-20
P0150.040-016-A4	M 4	16	2.8	8	4.5	3.2	6.0	TX-20
P0150.040-020-A4	M 4	20	2.8	8	4.5	3.2	6.0	TX-20
P0150.040-025-A4	M 4	25	2.8	8	4.5	3.2	6.0	TX-20
P0150.040-030-A4	M 4	30	2.8	8	4.5	3.2	6.0	TX-20
P0150.040-040-A4	M 4	40	2.8	8	4.5	3.2	6.0	TX-20
P0150.040-050-A4	M 4	50	2.8	8	4.5	3.2	6.0	TX-20
P0150.050-010-A4	M 5	10	3.7	10	5.5	3.9	7.5	TX-25
P0150.050-012-A4	M 5	12	3.7	10	5.5	3.9	7.5	TX-25
P0150.050-016-A4	M 5	16	3.7	10	5.5	3.9	7.5	TX-25
P0150.050-020-A4	M 5	20	3.7	10	5.5	3.9	7.5	TX-25
P0150.050-025-A4	M 5	25	3.7	10	5.5	3.9	7.5	TX-25
P0150.050-030-A4	M 5	30	3.7	10	5.5	3.9	7.5	TX-25
P0150.050-040-A4	M 5	40	3.7	10	5.5	3.9	7.5	TX-25
P0150.050-050-A4	M 5	50	3.7	10	5.5	3.9	7.5	TX-25
P0150.060-010-A4	M 6	10	4.2	12	6.5	4.7	7.5	TX-30
P0150.060-012-A4	M 6	12	4.2	12	6.5	4.7	7.5	TX-30
P0150.060-016-A4	M 6	16	4.2	12	6.5	4.7	7.5	TX-30



Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	d ₃ max.	d ₄ min.	h ₁ max.	l ₂ ±0.25	TX size
P0150.060-020-A4	M 6	20	4.2	12	6.5	4.7	7.5	TX-30
P0150.060-025-A4	M 6	25	4.2	12	6.5	4.7	7.5	TX-30
P0150.060-030-A4	M 6	30	4.2	12	6.5	4.7	7.5	TX-30
P0150.060-040-A4	M 6	40	4.2	12	6.5	4.7	7.5	TX-30
P0150.060-050-A4	M 6	50	4.2	12	6.5	4.7	7.5	TX-30
P0150.060-060-A4	M 6	60	4.2	12	6.5	4.7	7.5	TX-30
P0150.060-080-A4	M 6	80	4.2	12	6.5	4.7	7.5	TX-30
P0150.080-012-A4	M 8	12	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-016-A4	M 8	16	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-020-A4	M 8	20	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-025-A4	M 8	25	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-030-A4	M 8	30	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-035-A4	M 8	35	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-040-A4	M 8	40	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-045-A4	M 8	45	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-050-A4	M 8	50	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-060-A4	M 8	60	6.0	16	8.5	6.1	10.0	TX-30*
P0150.080-080-A4	M 8	80	6.0	16	8.5	6.1	10.0	TX-30*