




# Anti-Stiction Air Cylinder - 15.9mm

front stud mount, air extend, spring return



L4530

CYLINDERS

### Material

Carbon/graphite piston. Stainless steel rod (AISI 303). Stainless steel outer tube (AISI 304). Nickel plated aluminium cylinder heads and piston/rod coupling. Graphite filled bronze pivot bushing.

### Technical Notes

Ultra low friction.  
Corrosion resistant, no need for lubrication.

Operating temp range: -55°C to +150°C.  
For applications operating below -20°C please add -ET to part number. Suitable for vacuum actuation.  
Piston area = 198mm<sup>2</sup>.  
Force output at max pressure on rear side = 139N.  
Force output at max pressure on rod side = 125N.  
Piston friction as % of load (without side

load) = 1% - 2%.  
Min pressure differential required for actuation = <0.0015 MPa.  
Force factor rear side = 198N.  
Force factor rod side = 178N.  
(factor x pressure (MPa) = force output (N)).  
\*max leak measured at pressure of 0.34 MPa.

Order No.	Bore dia.	Stroke	Length	Pressure MPa max.	Leak rate by piston SL/min max.	Leak rate by rod SL/mm max.	Reset spring force rod extended N	Reset spring force rod retracted N	Weight g
L4530.012	15,9	12,5	69,5	0,7	139	125	1,1	1,0	72,38
L4530.025	15,9	25	82	0,7	139	125	1,1	0,9	80,15
L4530.037	15,9	37,5	94,5	0,7	139	125	1,1	0,8	87,93
L4530.050	15,9	50	107	0,7	139	125	1,1	0,7	95,70