




Ultra Low Head Cap Screws

hex. drive - titanium

Standard Screws



P0208.Ti

STANDARD SCREWS

Material

Titanium (ASTM B348 grades 2 and 5). Titanium has outstanding corrosion resistance and a very high strength-to-weight ratio. Grade 2 titanium is pure titanium and


grade 5 titanium is the alloy Ti6Al4V.

Technical Notes

The ultra low head is extremely low profile. These screws do not require a countersunk

location hole. Most suitable for machine and equipment applications with minimal clearance.

Order No.	d ₁	l ₁	d ₂	h ₁	h ₂ max.	h ₃ max.	r ₁ min.	A/F	Torque to Nm max.	Material grade
P0208.020-003-T2	M 2	3	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 2
P0208.020-004-T2	M 2	4	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 2
P0208.020-005-T2	M 2	5	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 2
P0208.020-006-T2	M 2	6	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 2
P0208.020-008-T2	M 2	8	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 2
P0208.020-010-T2	M 2	10	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 2
P0208.025-003-T2	M 2,5	3	5	0.6	1.5	1.2	0.10	1.3	0.35	titanium grade 2
P0208.025-004-T2	M 2,5	4	5	0.6	1.5	1.2	0.10	1.3	0.35	titanium grade 2
P0208.025-005-T2	M 2,5	5	5	0.6	1.5	1.2	0.10	1.3	0.35	titanium grade 2
P0208.025-006-T2	M 2,5	6	5	0.6	1.5	1.2	0.10	1.3	0.35	titanium grade 2
P0208.030-005-T2	M 3	5	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 2
P0208.030-006-T2	M 3	6	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 2
P0208.030-008-T2	M 3	8	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 2
P0208.030-010-T2	M 3	10	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 2
P0208.030-012-T2	M 3	12	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 2
P0208.030-016-T2	M 3	16	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 2
P0208.040-005-T2	M 4	5	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 2
P0208.040-006-T2	M 4	6	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 2
P0208.040-008-T2	M 4	8	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 2
P0208.040-010-T2	M 4	10	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 2
P0208.040-012-T2	M 4	12	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 2
P0208.040-016-T2	M 4	16	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 2
P0208.040-020-T2	M 4	20	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 2
P0208.040-025-T2	M 4	25	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 2
P0208.050-006-T2	M 5	6	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 2
P0208.050-008-T2	M 5	8	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 2
P0208.050-010-T2	M 5	10	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 2
P0208.050-012-T2	M 5	12	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 2
P0208.050-016-T2	M 5	16	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 2
P0208.050-020-T2	M 5	20	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 2
P0208.050-025-T2	M 5	25	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 2
P0208.060-008-T2	M 6	8	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 2



Order No.	d ₁	l ₁	d ₂	h ₁	h ₂ max.	h ₃ max.	r ₁ min.	A/F	Torque to Nm max.	Material grade
P0208.060-010-T2	M 6	10	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 2
P0208.060-012-T2	M 6	12	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 2
P0208.060-016-T2	M 6	16	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 2
P0208.060-020-T2	M 6	20	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 2
P0208.060-025-T2	M 6	25	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 2
P0208.020-003-T5	M 2	3	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 5
P0208.020-004-T5	M 2	4	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 5
P0208.020-005-T5	M 2	5	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 5
P0208.020-006-T5	M 2	6	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 5
P0208.020-008-T5	M 2	8	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 5
P0208.020-010-T5	M 2	10	4	0.5	1.2	1.2	0.10	1.3	0.16	titanium grade 5
P0208.025-003-T5	M 2,5	3	5	0.6	1.5	1.2	0.10	1.3	0.35	titanium grade 5
P0208.025-004-T5	M 2,5	4	5	0.6	1.5	1.2	0.10	1.3	0.35	titanium grade 5
P0208.025-005-T5	M 2,5	5	5	0.6	1.5	1.2	0.10	1.3	0.35	titanium grade 5
P0208.025-006-T5	M 2,5	6	5	0.6	1.5	1.2	0.10	1.3	0.35	titanium grade 5
P0208.030-005-T5	M 3	5	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 5
P0208.030-006-T5	M 3	6	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 5
P0208.030-008-T5	M 3	8	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 5
P0208.030-010-T5	M 3	10	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 5
P0208.030-012-T5	M 3	12	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 5
P0208.030-016-T5	M 3	16	6	0.8	2.0	1.4	0.10	1.5	0.60	titanium grade 5
P0208.040-005-T5	M 4	5	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 5
P0208.040-006-T5	M 4	6	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 5
P0208.040-008-T5	M 4	8	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 5
P0208.040-010-T5	M 4	10	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 5
P0208.040-012-T5	M 4	12	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 5
P0208.040-016-T5	M 4	16	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 5
P0208.040-020-T5	M 4	20	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 5
P0208.040-025-T5	M 4	25	8	0.9	2.5	1.5	0.20	2.0	1.10	titanium grade 5
P0208.050-006-T5	M 5	6	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 5
P0208.050-008-T5	M 5	8	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 5
P0208.050-010-T5	M 5	10	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 5
P0208.050-012-T5	M 5	12	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 5
P0208.050-016-T5	M 5	16	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 5
P0208.050-020-T5	M 5	20	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 5
P0208.050-025-T5	M 5	25	9	1.0	3.0	1.8	0.20	2.5	2.20	titanium grade 5
P0208.060-008-T5	M 6	8	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 5
P0208.060-010-T5	M 6	10	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 5
P0208.060-012-T5	M 6	12	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 5
P0208.060-016-T5	M 6	16	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 5
P0208.060-020-T5	M 6	20	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 5
P0208.060-025-T5	M 6	25	10	1.2	4.0	2.2	0.25	3.0	5.00	titanium grade 5