




Cylinder / Piston Set

0,366" bore

Cylinders



L4632

CYLINDERS

Material

Piston: Carbon graphite
Cylinder: Glass

Technical Notes

Max operating temp = 260°C

Important Notes

Specials available on request.

Order No.	Stroke	Bore dia.	Outside dia.	Cylinder length	Piston length	Piston area in ²	Friction W/O sideload g	Cylinder weight g	Piston weight g
L4632.0500	0,5"	0.336	0.462	0,975"	0.375	0.105	< 1	2.29	0.77
L4632.1000	1,0"	0.336	0.462	1,475"	0.375	0.105	< 1	2.29	0.77
L4632.2000	2,0"	0.336	0.462	2,475"	0.375	0.105	< 1	2.29	0.77
L4632.3000	3,0"	0.336	0.462	3,475"	0.375	0.105	< 1	2.29	0.77
L4632.4000	4,0"	0.336	0.462	4,475"	0.375	0.105	< 1	2.29	0.77
L4632.5000	5,0"	0.336	0.462	5,475"	0.375	0.105	< 1	2.29	0.77
L4632.6000	6,0"	0.336	0.462	6,475"	0.375	0.105	< 1	2.29	0.77
L4632.7000	7,0"	0.336	0.462	7,475"	0.375	0.105	< 1	2.29	0.77
L4632.8000	8,0"	0.336	0.462	8,475"	0.375	0.105	< 1	2.29	0.77