






# Full Nuts Fine Thread

## A2 stainless



**P0302.A2**

NUTS

### Material

Stainless steel (A2).

### Technical Notes

DIN 934. Fine pitch threads.

For coarse thread full nuts see P0301.

| Order No.        | d <sub>1</sub> | h <sub>1</sub><br>min. | A/F | Material |
|------------------|----------------|------------------------|-----|----------|
| P0302.080-100-A2 | M08x1,0        | 6.14                   | 13  | A2 s/s   |
| P0302.100-100-A2 | M10x1,0        | 7.64                   | 17  | A2 s/s   |
| P0302.100-125-A2 | M10x1,25       | 7.64                   | 17  | A2 s/s   |
| P0302.120-125-A2 | M12x1,25       | 9.64                   | 19  | A2 s/s   |
| P0302.120-150-A2 | M12x1,5        | 9.64                   | 19  | A2 s/s   |
| P0302.140-150-A2 | M14x1,5        | 10.3                   | 22  | A2 s/s   |
| P0302.160-150-A2 | M16x1,5        | 12.3                   | 24  | A2 s/s   |
| P0302.180-150-A2 | M18x1,5        | 14.3                   | 27  | A2 s/s   |
| P0302.200-150-A2 | M20x1,5        | 14.9                   | 30  | A2 s/s   |
| P0302.200-200-A2 | M20x2,0        | 14.9                   | 30  | A2 s/s   |
| P0302.220-150-A2 | M22x1,5        | 16.9                   | 32  | A2 s/s   |
| P0302.240-150-A2 | M24x1,5        | 17.7                   | 36  | A2 s/s   |
| P0302.240-200-A2 | M24x2,0        | 17.7                   | 36  | A2 s/s   |
| P0302.270-150-A2 | M27x1,5        | 20.7                   | 41  | A2 s/s   |
| P0302.270-200-A2 | M27x2,0        | 20.7                   | 41  | A2 s/s   |
| P0302.300-200-A2 | M30x2,0        | 22.7                   | 46  | A2 s/s   |
| P0302.300-150-A2 | M30x1,5        | 22.7                   | 46  | A2 s/s   |
| P0302.360-150-A2 | M36x1,5        | 27.4                   | 55  | A2 s/s   |
| P0302.360-300-A2 | M36x3,0        | 27.4                   | 55  | A2 s/s   |