




Cylinder / Piston Set

0,945" bore

Cylinders



L4636

CYLINDERS

Material

Piston: Carbon graphite
Cylinder: Glass

Technical Notes

Max operating temp = 260°C

Important Notes

Specials available on request.

Order No.	Stroke	Bore dia.	Outside dia.	Cylinder length	Piston length	Piston area in ²	Friction W/O sideload g	Cylinder weight g	Piston weight g
L4636.0500	0,5"	0.945	1.088	1,105"	0.505	0.701	< 1	8.39	4.66
L4636.1000	1,0"	0.945	1.088	1,605"	0.505	0.701	< 1	8.39	4.66
L4636.2000	2,0"	0.945	1.088	2,605"	0.505	0.701	< 1	8.39	4.66
L4636.3000	3,0"	0.945	1.088	3,605"	0.505	0.701	< 1	8.39	4.66
L4636.4000	4,0"	0.945	1.088	4,605"	0.505	0.701	< 1	8.39	4.66
L4636.5000	5,0"	0.945	1.088	5,605"	0.505	0.701	< 1	8.39	4.66
L4636.6000	6,0"	0.945	1.088	6,605"	0.505	0.701	< 1	8.39	4.66
L4636.7000	7,0"	0.945	1.088	7,605"	0.505	0.701	< 1	8.39	4.66
L4636.8000	8,0"	0.945	1.088	8,605"	0.505	0.701	< 1	8.39	4.66