






# Round Rivet Bushes

## Aluminium

### Rivet Bushes



**P0828.AL**

RIVET BUSHES

#### Material

Aluminium.

#### Technical Notes

Rivet bushes are securely locked by means

of a thin spigot. The presence of serrations provide additional anchorage.

These bushes can be installed by a press or using a hammer.

| Order No.        | d <sub>1</sub> | Panel thickness | w <sub>1</sub> | d <sub>2</sub> | d <sub>3</sub> | h <sub>1</sub> | For gauge |
|------------------|----------------|-----------------|----------------|----------------|----------------|----------------|-----------|
| P0828.030-22G-AL | M 3            | 0.8             | 1,3-1,5        | 5.54           | 7.92           | 3.17           | 22G       |
| P0828.030-20G-AL | M 3            | 1.0             | 1,5-1,7        | 5.54           | 7.92           | 3.17           | 20G       |
| P0828.030-18G-AL | M 3            | 1.2             | 1,7-1,9        | 5.54           | 7.92           | 3.17           | 18G       |
| P0828.030-16G-AL | M 3            | 1.5             | 2,0-2,2        | 5.54           | 7.92           | 3.17           | 16G       |
| P0828.030-14G-AL | M 3            | 2.0             | 2,5-2,7        | 5.54           | 7.92           | 3.17           | 14G       |
| P0828.030-12G-AL | M 3            | 2.5             | 3,0-3,2        | 5.54           | 7.92           | 3.17           | 12G       |
| P0828.030-10G-AL | M 3            | 3.0             | 3,5-3,7        | 5.54           | 7.92           | 3.17           | 10G       |
| P0828.030-08G-AL | M 3            | 4.0             | 4,5-4,7        | 5.54           | 7.92           | 3.17           | 8G        |
| P0828.035-22G-AL | M3,5           | 0.8             | 1,3-1,5        | 5.54           | 7.92           | 3.17           | 22G       |
| P0828.035-20G-AL | M3,5           | 1.0             | 1,5-1,7        | 5.54           | 7.92           | 3.17           | 20G       |
| P0828.035-18G-AL | M3,5           | 1.2             | 1,7-1,9        | 5.54           | 7.92           | 3.17           | 18G       |
| P0828.035-16G-AL | M3,5           | 1.5             | 2,0-2,2        | 5.54           | 7.92           | 3.17           | 16G       |
| P0828.035-14G-AL | M3,5           | 2.0             | 2,5-2,7        | 5.54           | 7.92           | 3.17           | 14G       |
| P0828.035-12G-AL | M3,5           | 2.5             | 3,0-3,2        | 5.54           | 7.92           | 3.17           | 12G       |
| P0828.035-10G-AL | M3,5           | 3.0             | 3,5-3,7        | 5.54           | 7.92           | 3.17           | 10G       |
| P0828.035-08G-AL | M3,5           | 4.0             | 4,5-4,7        | 5.54           | 7.92           | 3.17           | 8G        |
| P0828.040-22G-AL | M 4            | 0.8             | 1,3-1,5        | 6.73           | 7.92           | 3.17           | 22G       |
| P0828.040-20G-AL | M 4            | 1.0             | 1,5-1,7        | 6.73           | 7.92           | 3.17           | 20G       |
| P0828.040-18G-AL | M 4            | 1.2             | 1,7-1,9        | 6.73           | 7.92           | 3.17           | 18G       |
| P0828.040-16G-AL | M 4            | 1.5             | 2,0-2,2        | 6.73           | 7.92           | 3.17           | 16G       |
| P0828.040-14G-AL | M 4            | 2.0             | 2,5-2,7        | 6.73           | 7.92           | 3.17           | 14G       |
| P0828.040-12G-AL | M 4            | 2.5             | 3,0-3,2        | 6.73           | 7.92           | 3.17           | 12G       |
| P0828.040-10G-AL | M 4            | 3.0             | 3,5-3,7        | 6.73           | 7.92           | 3.17           | 10G       |
| P0828.040-08G-AL | M 4            | 4.0             | 4,5-4,7        | 6.73           | 7.92           | 3.17           | 8G        |
| P0828.050-22G-AL | M 5            | 0.8             | 1,3-1,5        | 7.92           | 9.52           | 3.81           | 22G       |
| P0828.050-20G-AL | M 5            | 1.0             | 1,5-1,7        | 7.92           | 9.52           | 3.81           | 20G       |
| P0828.050-18G-AL | M 5            | 1.2             | 1,7-1,9        | 7.92           | 9.52           | 3.81           | 18G       |
| P0828.050-16G-AL | M 5            | 1.5             | 2,0-2,2        | 7.92           | 9.52           | 3.81           | 16G       |
| P0828.050-14G-AL | M 5            | 2.0             | 2,5-2,7        | 7.92           | 9.52           | 3.81           | 14G       |
| P0828.050-12G-AL | M 5            | 2.5             | 3,0-3,2        | 7.92           | 9.52           | 3.81           | 12G       |
| P0828.050-10G-AL | M 5            | 3.0             | 3,5-3,7        | 7.92           | 9.52           | 3.81           | 10G       |
| P0828.050-08G-AL | M 5            | 4.0             | 4,5-4,7        | 7.92           | 9.52           | 3.81           | 8G        |
| P0828.060-22G-AL | M 6            | 0.8             | 1,3-1,5        | 9.52           | 11.1           | 5.08           | 22G       |
| P0828.060-20G-AL | M 6            | 1.0             | 1,5-1,7        | 9.52           | 11.1           | 5.08           | 20G       |



**Automotion**  
AN ESSENTIA COMPANY

0333 207 4498

[sales@automotioncomponents.co.uk](mailto:sales@automotioncomponents.co.uk)



# Round Rivet Bushes

## Aluminium



RIVET BUSHES

| Order No.        | d <sub>1</sub> | Panel thickness | w <sub>1</sub> | d <sub>2</sub> | d <sub>3</sub> | h <sub>1</sub> | For gauge |
|------------------|----------------|-----------------|----------------|----------------|----------------|----------------|-----------|
| P0828.060-18G-AL | M 6            | 1.2             | 1,7-1,9        | 9.52           | 11.1           | 5.08           | 18G       |
| P0828.060-16G-AL | M 6            | 1.5             | 2,0-2,2        | 9.52           | 11.1           | 5.08           | 16G       |
| P0828.060-14G-AL | M 6            | 2.0             | 2,5-2,7        | 9.52           | 11.1           | 5.08           | 14G       |
| P0828.060-12G-AL | M 6            | 2.5             | 3,0-3,2        | 9.52           | 11.1           | 5.08           | 12G       |
| P0828.060-10G-AL | M 6            | 3.0             | 3,5-3,7        | 9.52           | 11.1           | 5.08           | 10G       |
| P0828.060-08G-AL | M 6            | 4.0             | 4,5-4,7        | 9.52           | 11.1           | 5.08           | 8G        |
| P0828.080-22G-AL | M 8            | 0.8             | 1,3-1,5        | 12.7           | 14.27          | 6.35           | 22G       |
| P0828.080-20G-AL | M 8            | 1.0             | 1,5-1,7        | 12.7           | 14.27          | 6.35           | 20G       |
| P0828.080-18G-AL | M 8            | 1.2             | 1,7-1,9        | 12.7           | 14.27          | 6.35           | 18G       |
| P0828.080-16G-AL | M 8            | 1.5             | 2,0-2,2        | 12.7           | 14.27          | 6.35           | 16G       |
| P0828.080-14G-AL | M 8            | 2.0             | 2,5-2,7        | 12.7           | 14.27          | 6.35           | 14G       |
| P0828.080-12G-AL | M 8            | 2.5             | 3,0-3,2        | 12.7           | 14.27          | 6.35           | 12G       |
| P0828.080-10G-AL | M 8            | 3.0             | 3,5-3,7        | 12.7           | 14.27          | 6.35           | 10G       |
| P0828.080-08G-AL | M 8            | 4.0             | 4,5-4,7        | 12.7           | 14.27          | 6.35           | 8G        |
| P0828.100-22G-AL | M10            | 0.8             | 1,3-1,5        | 15.87          | 19.05          | 7.62           | 22G       |
| P0828.100-20G-AL | M10            | 1.0             | 1,5-1,7        | 15.87          | 19.05          | 7.62           | 20G       |
| P0828.100-18G-AL | M10            | 1.2             | 1,7-1,9        | 15.87          | 19.05          | 7.62           | 18G       |
| P0828.100-16G-AL | M10            | 1.5             | 2,0-2,2        | 15.87          | 19.05          | 7.62           | 16G       |
| P0828.100-14G-AL | M10            | 2.0             | 2,5-2,7        | 15.87          | 19.05          | 7.62           | 14G       |
| P0828.100-12G-AL | M10            | 2.5             | 3,0-3,2        | 15.87          | 19.05          | 7.62           | 12G       |
| P0828.100-10G-AL | M10            | 3.0             | 3,5-3,7        | 15.87          | 19.05          | 7.62           | 10G       |
| P0828.100-08G-AL | M10            | 4.0             | 4,5-4,7        | 15.87          | 19.05          | 7.62           | 8G        |
| P0828.120-22G-AL | M12            | 0.8             | 1,3-1,5        | 19.05          | 22.22          | 10.16          | 22G       |
| P0828.120-20G-AL | M12            | 1.0             | 1,5-1,7        | 19.05          | 22.22          | 10.16          | 20G       |
| P0828.120-18G-AL | M12            | 1.2             | 1,7-1,9        | 19.05          | 22.22          | 10.16          | 18G       |
| P0828.120-16G-AL | M12            | 1.5             | 2,0-2,2        | 19.05          | 22.22          | 10.16          | 16G       |
| P0828.120-14G-AL | M12            | 2.0             | 2,5-2,7        | 19.05          | 22.22          | 10.16          | 14G       |
| P0828.120-12G-AL | M12            | 2.5             | 3,0-3,2        | 19.05          | 22.22          | 10.16          | 12G       |
| P0828.120-10G-AL | M12            | 3.0             | 3,5-3,7        | 19.05          | 22.22          | 10.16          | 10G       |
| P0828.120-08G-AL | M12            | 4.0             | 4,5-4,7        | 19.05          | 22.22          | 10.16          | 8G        |