






## CD Weldstud Copper coated

## Weld Studs



**P0830.CU**

WELD STUDS

### Material

Steel, copper coated.

### Technical Notes

CD weld studs have a small nub under their

end which melts to form the weld. When the nub disintegrates it melts and helps solidify the weld to the base material. CD stud welding is often used for smaller

diameter studs and pins, as well as on non-standard materials and for accuracy.

| Order No.        | d <sub>1</sub> | d <sub>2</sub> | l <sub>1</sub> |
|------------------|----------------|----------------|----------------|
| P0830.030-006-CU | M3             | 4.5            | 6              |
| P0830.030-008-CU | M3             | 4.5            | 8              |
| P0830.030-010-CU | M3             | 4.5            | 10             |
| P0830.030-012-CU | M3             | 4.5            | 12             |
| P0830.030-015-CU | M3             | 4.5            | 15             |
| P0830.030-016-CU | M3             | 4.5            | 16             |
| P0830.030-020-CU | M3             | 4.5            | 20             |
| P0830.030-025-CU | M3             | 4.5            | 25             |
| P0830.030-030-CU | M3             | 4.5            | 30             |
| P0830.030-035-CU | M3             | 4.5            | 35             |
| P0830.030-040-CU | M3             | 4.5            | 40             |
| P0830.030-050-CU | M3             | 4.5            | 50             |
| P0830.040-006-CU | M4             | 5.5            | 6              |
| P0830.040-008-CU | M4             | 5.5            | 8              |
| P0830.040-010-CU | M4             | 5.5            | 10             |
| P0830.040-012-CU | M4             | 5.5            | 12             |
| P0830.040-015-CU | M4             | 5.5            | 15             |
| P0830.040-016-CU | M4             | 5.5            | 16             |
| P0830.040-020-CU | M4             | 5.5            | 20             |
| P0830.040-025-CU | M4             | 5.5            | 25             |
| P0830.040-030-CU | M4             | 5.5            | 30             |
| P0830.040-035-CU | M4             | 5.5            | 35             |
| P0830.040-040-CU | M4             | 5.5            | 40             |
| P0830.040-045-CU | M4             | 5.5            | 45             |
| P0830.040-050-CU | M4             | 5.5            | 50             |
| P0830.050-006-CU | M5             | 6.5            | 6              |
| P0830.050-008-CU | M5             | 6.5            | 8              |
| P0830.050-010-CU | M5             | 6.5            | 10             |
| P0830.050-012-CU | M5             | 6.5            | 12             |
| P0830.050-015-CU | M5             | 6.5            | 15             |
| P0830.050-016-CU | M5             | 6.5            | 16             |
| P0830.050-020-CU | M5             | 6.5            | 20             |
| P0830.050-025-CU | M5             | 6.5            | 25             |
| P0830.050-030-CU | M5             | 6.5            | 30             |





| Order No.        | d <sub>1</sub> | d <sub>2</sub> | l <sub>1</sub> |
|------------------|----------------|----------------|----------------|
| P0830.050-035-CU | M5             | 6.5            | 35             |
| P0830.050-040-CU | M5             | 6.5            | 40             |
| P0830.050-045-CU | M5             | 6.5            | 45             |
| P0830.050-050-CU | M5             | 6.5            | 50             |
| P0830.050-060-CU | M5             | 6.5            | 60             |
| P0830.060-008-CU | M6             | 7.5            | 8              |
| P0830.060-010-CU | M6             | 7.5            | 10             |
| P0830.060-012-CU | M6             | 7.5            | 12             |
| P0830.060-014-CU | M6             | 7.5            | 14             |
| P0830.060-015-CU | M6             | 7.5            | 15             |
| P0830.060-016-CU | M6             | 7.5            | 16             |
| P0830.060-020-CU | M6             | 7.5            | 20             |
| P0830.060-025-CU | M6             | 7.5            | 25             |
| P0830.060-030-CU | M6             | 7.5            | 30             |
| P0830.060-035-CU | M6             | 7.5            | 35             |
| P0830.060-040-CU | M6             | 7.5            | 40             |
| P0830.060-045-CU | M6             | 7.5            | 45             |
| P0830.060-050-CU | M6             | 7.5            | 50             |
| P0830.060-055-CU | M6             | 7.5            | 55             |
| P0830.060-060-CU | M6             | 7.5            | 60             |
| P0830.080-010-CU | M8             | 9.0            | 10             |
| P0830.080-012-CU | M8             | 9.0            | 12             |
| P0830.080-014-CU | M8             | 9.0            | 14             |
| P0830.080-015-CU | M8             | 9.0            | 15             |
| P0830.080-016-CU | M8             | 9.0            | 16             |
| P0830.080-020-CU | M8             | 9.0            | 20             |
| P0830.080-025-CU | M8             | 9.0            | 25             |
| P0830.080-030-CU | M8             | 9.0            | 30             |
| P0830.080-035-CU | M8             | 9.0            | 35             |
| P0830.080-040-CU | M8             | 9.0            | 40             |
| P0830.080-045-CU | M8             | 9.0            | 45             |
| P0830.080-050-CU | M8             | 9.0            | 50             |
| P0830.080-055-CU | M8             | 9.0            | 55             |
| P0830.080-060-CU | M8             | 9.0            | 60             |