




Steel Shoulder Bolts - Hex. Head construction grade

Shoulder Screws



P0142.SC

SHOULDER SCREWS

Material

Black alloy steel, strength 8.8. Hardness 38 HRC, tensile strength 830 N/mm².

Technical Notes


To DIN 7968

Tips

Do not tighten to standard strength class 8.8 torque; as the tightening torque is limited, by the presence of the reduced diameter


undercut under the head and at the shoulder/thread area.

Order No.	d ₁	d ₂ tol. h11	l ₁	l ₂	h ₁	A/F
P0142.120-035-SC	M12	12.74	35	20.5	8	18
P0142.120-040-SC	M12	12.74	40	20.5	8	18
P0142.120-045-SC	M12	12.74	45	20.5	8	18
P0142.120-050-SC	M12	12.74	50	20.5	8	18
P0142.120-055-SC	M12	12.74	55	20.5	8	18
P0142.120-060-SC	M12	12.74	60	20.5	8	18
P0142.120-070-SC	M12	12.74	70	20.5	8	18
P0142.120-075-SC	M12	12.74	75	20.5	8	18
P0142.160-040-SC	M16	16.74	40	24.5	10	24
P0142.160-045-SC	M16	16.74	45	24.5	10	24
P0142.160-050-SC	M16	16.74	50	24.5	10	24
P0142.160-055-SC	M16	16.74	55	24.5	10	24
P0142.160-060-SC	M16	16.74	60	24.5	10	24
P0142.160-065-SC	M16	16.74	65	24.5	10	24
P0142.160-070-SC	M16	16.74	70	24.5	10	24
P0142.160-080-SC	M16	16.74	80	24.5	10	24
P0142.160-085-SC	M16	16.74	85	24.5	10	24
P0142.200-050-SC	M20	20.71	50	28.5	13	30
P0142.200-055-SC	M20	20.71	55	28.5	13	30
P0142.200-060-SC	M20	20.71	60	28.5	13	30
P0142.200-065-SC	M20	20.71	65	28.5	13	30
P0142.200-070-SC	M20	20.71	70	28.5	13	30
P0142.200-075-SC	M20	20.71	75	28.5	13	30
P0142.200-080-SC	M20	20.71	80	28.5	13	30
P0142.200-090-SC	M20	20.71	90	28.5	13	30
P0142.200-100-SC	M20	20.71	100	28.5	13	30
P0142.200-110-SC	M20	20.71	110	28.5	13	30
P0142.240-060-SC	M24	24.71	60	33.0	15	36
P0142.240-065-SC	M24	24.71	65	33.0	15	36
P0142.240-070-SC	M24	24.71	70	33.0	15	36
P0142.240-075-SC	M24	24.71	75	33.0	15	36
P0142.240-080-SC	M24	24.71	80	33.0	15	36



Shoulder Screws

Steel Shoulder Bolts - Hex. Head construction grade



Order No.	d ₁	d ₂ tol. h11	l ₁	l ₂	h ₁	A/F
P0142.240-085-SC	M24	24.71	85	33.0	15	36
P0142.240-090-SC	M24	24.71	90	33.0	15	36
P0142.240-100-SC	M24	24.71	100	33.0	15	36
P0142.240-120-SC	M24	24.71	120	33.0	15	36
P0142.240-165-SC	M24	24.71	160	33.0	15	36
P0142.240-195-SC	M24	24.71	195	33.0	15	36
P0142.270-090-SC	M27	27.71	90	33.5	17	41
P0142.270-100-SC	M27	27.71	100	33.5	17	41
P0142.270-110-SC	M27	27.71	110	33.5	17	41

SHOULDER SCREWS



Product Overview

Shoulder Screws & Shoulder Bolts



SHOULDER SCREWS

Steel shoulder screws

These are our least expensive option. They are produced to ISO 7379 standards.

Thread sizes from Ø4 M3 to Ø24 M20. We manufacture special shoulder screws to customer drawings with a minimum batch size.



Stainless steel shoulder screws

We have three different grades of stainless steel shoulder screws:

303 series – these are our standard grade of stainless (P0130.A2). They are strong and resistant to corrosion but not to very harsh environments such as salt water.

416 series – these are made from harder stainless steel with improved shear strengths but the parts are more prone to corrosion (see part no. P0131 and P0133).

316 series – these shoulder screws (P0130.A4) are very resistant to corrosion but are considerably more expensive than other stainless versions.



Shoulder bolts

Our range of precision shoulder bolts with hexagonal heads come in both steel (grades 8.8 and 10.9) and stainless steel (303 and 316 stainless). These bolts are manufactured to DIN 609 and DIN 610. We also have shoulder bolts for construction, manufactured to DIN 7968.

	DIN 609 standard length thread	DIN 610 short length thread	DIN 7968 construction
			
Grade 8.8 steel	P0138.SC	P0140.SC	P0142
Grade 10.9 steel	P0139	P0141	-
303 stainless steel	P0138.A2	P0140.A2	-




Automotion
AN ESSENTA COMPANY

0333 207 4498

sales@automotioncomponents.co.uk



Shoulder Screw from Automation Components

Part No.		Material	Head	Corrosion resistance	Strength	Ø/thread	DIN/ISO
P0130		303 stainless steel	Hex socket	✓✓	✓	Min: Ø4/M3 Max: Ø20/M16	-
P0130.A4		316 stainless steel	Hex socket	✓✓✓	✓	Min: Ø4/M3 Max: Ø20/M16	ISO 7379
P0131		416 stainless steel	Hex socket	✓	✓✓	Min: Ø4/M3 Max: Ø12/M10	-
P0132		303 stainless steel	Slotted	✓✓	✓	Min: Ø4/M3 Max: Ø12/M10	-
P0133		416 stainless steel	Slotted	✓	✓✓	Min: Ø4/M3 Max: Ø12/M10	-
P0134		303 stainless steel	Hex socket	✓✓	✓	Min: Ø4/M3 Max: Ø8/M6	-
P0135		303 stainless steel	Hex head	✓✓	✓	Min: Ø4/M3 Max: Ø12/M10	-
P0136		Steel 12,9	Hex socket	X	✓✓	Min: Ø4/M3 Max: Ø24/M20	ISO 7379
P0137		304 stainless steel	Hex socket	✓✓	✓	Min: Ø6/M5 Max: Ø20/M16	ISO 7379
P0138		Steel 8,8	Hex head (long thread)	X	✓	Min: Ø9/M8 Max: Ø44/M42	DIN 610
P0139		Steel 10,9	Hex head (long thread)	X	✓✓	Min: Ø9/M8 Max: Ø38/M36	DIN 610
P0140		Steel 8,8	Hex socket (short thread)	X	✓✓	Min: Ø9/M8 Max: Ø44/M42	DIN 609
P0141		Steel 10,9	Hex socket (short thread)	X	✓✓	Min: Ø9/M8 Max: Ø38/M36	DIN 609
P0142		Steel 8,8	Hex head	X	✓✓	Min: Ø12/M12 Max: Ø27/M27	DIN 7968
P0144		303 stainless steel	Pan head	✓✓	✓✓	Min: Ø4/M3 Max: Ø10/M8	DIN 923