




Captive Screws - Cap Head

TX drive - 316 stainless, blackened



Captive Screws



P0156.B4

CAPTIVE SCREWS

Material

Stainless steel (AISI 316, 1.440), black oxide coating. Tensile strength 480 N/mm². Proof stress min. 200 N/mm², austenitic stainless steel.

Also available on request in steel (anodised, black oxide or zinc plated) stainless steel (AISI 303, 1.4305), brass, aluminium etc.

Technical Notes


Used to comply with the Machinery Directive 2006/42/EC. Generally to ISO 4762. Often used with our captive washers (P0168) or retaining flanges (P0169.A2 - for sheet metal applications). The use of our captive washers should be considered when fitted in panels with unthreaded holes.

*M 8 sizes have a reduced TX size.

Important Notes

Please note that these screws have a reduced diameter shank and should not be tightened to the recommended torque for an equivalent machine screw of size d₁.

Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	l ₂ ±0.25	d ₃ max.	d ₄ min.	h ₁ max.	TX size
P0156.030-008-B4	M 3	8	2.0	4.5	5.5	3.5	3	TX-10
P0156.030-010-B4	M 3	10	2.0	4.5	5.5	3.5	3	TX-10
P0156.030-016-B4	M 3	16	2.0	4.5	5.5	3.5	3	TX-10
P0156.030-020-B4	M 3	20	2.0	4.5	5.5	3.5	3	TX-10
P0156.030-025-B4	M 3	25	2.0	4.5	5.5	3.5	3	TX-10
P0156.030-030-B4	M 3	30	2.0	4.5	5.5	3.5	3	TX-10
P0156.040-008-B4	M 4	8	2.8	6.0	7.0	4.5	4	TX-20
P0156.040-010-B4	M 4	10	2.8	6.0	7.0	4.5	4	TX-20
P0156.040-012-B4	M 4	12	2.8	6.0	7.0	4.5	4	TX-20
P0156.040-016-B4	M 4	16	2.8	6.0	7.0	4.5	4	TX-20
P0156.040-020-B4	M 4	20	2.8	6.0	7.0	4.5	4	TX-20
P0156.040-025-B4	M 4	25	2.8	6.0	7.0	4.5	4	TX-20
P0156.040-030-B4	M 4	30	2.8	6.0	7.0	4.5	4	TX-20
P0156.040-040-B4	M 4	40	2.8	6.0	7.0	4.5	4	TX-20
P0156.040-050-B4	M 4	50	2.8	6.0	7.0	4.5	4	TX-20
P0156.050-010-B4	M 5	10	3.7	7.5	8.5	5.5	5	TX-25
P0156.050-012-B4	M 5	12	3.7	7.5	8.5	5.5	5	TX-25
P0156.050-016-B4	M 5	16	3.7	7.5	8.5	5.5	5	TX-25
P0156.050-020-B4	M 5	20	3.7	7.5	8.5	5.5	5	TX-25
P0156.050-025-B4	M 5	25	3.7	7.5	8.5	5.5	5	TX-25
P0156.050-030-B4	M 5	30	3.7	7.5	8.5	5.5	5	TX-25
P0156.050-040-B4	M 5	40	3.7	7.5	8.5	5.5	5	TX-25
P0156.050-050-B4	M 5	50	3.7	7.5	8.5	5.5	5	TX-25
P0156.060-010-B4	M 6	10	4.2	7.5	10.0	6.5	6	TX-30
P0156.060-012-B4	M 6	12	4.2	7.5	10.0	6.5	6	TX-30
P0156.060-016-B4	M 6	16	4.2	7.5	10.0	6.5	6	TX-30
P0156.060-020-B4	M 6	20	4.2	7.5	10.0	6.5	6	TX-30
P0156.060-025-B4	M 6	25	4.2	7.5	10.0	6.5	6	TX-30



Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	l ₂ ±0.25	d ₃ max.	d ₄ min.	h ₁ max.	TX size
P0156.060-030-B4	M 6	30	4.2	7.5	10.0	6.5	6	TX-30
P0156.060-040-B4	M 6	40	4.2	7.5	10.0	6.5	6	TX-30
P0156.060-050-B4	M 6	50	4.2	7.5	10.0	6.5	6	TX-30
P0156.060-060-B4	M 6	60	4.2	7.5	10.0	6.5	6	TX-30
P0156.060-080-B4	M 6	80	4.2	7.5	10.0	6.5	6	TX-30
P0156.080-012-B4	M 8	12	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-016-B4	M 8	16	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-020-B4	M 8	20	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-025-B4	M 8	25	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-030-B4	M 8	30	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-035-B4	M 8	35	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-040-B4	M 8	40	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-045-B4	M 8	45	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-050-B4	M 8	50	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-060-B4	M 8	60	6.0	10.0	13.0	8.5	8	TX-30*
P0156.080-080-B4	M 8	80	6.0	10.0	13.0	8.5	8	TX-30*