




Detent Pin Steel



P1250.2

OTHER PINS

Material

Shaft: Carbon steel (C1144), zinc plated.
Ball & spring: Stainless steel AISI 316.

Technical Notes

Detent pins are very economical for use in commercial and military equipment. The solid body with direct spring loaded

ball ensures reliable operation.

Can be used for locking telescopic tubing, securing bracket assemblies, as anchor clevis fittings, hinge pins and as replacement for cotter pins where frequent removal is necessary.

Hole sizes - commercial drills provide clear-


ance for our standard pins.

Inch dimensions in brackets ().

Tips

Also available in stainless steel see part no. P1252.2

Order No.	d_1 +0.00 -0.08	l_1 grip +1.50 -0.00	d_2	d_3	l_2	l_3	Pull out strength kg	Single shear strength kN min.
P1250.056-100	14,2 (9/16")	25,4 (1")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-120	14,2 (9/16")	30,5 (1,2")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-140	14,2 (9/16")	35,6 (1,4")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-160	14,2 (9/16")	40,6 (1,6")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-180	14,2 (9/16")	45,7 (1,8")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-200	14,2 (9/16")	50,8 (2")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-220	14,2 (9/16")	55,9 (2,2")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-240	14,2 (9/16")	61,0 (2,4")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-260	14,2 (9/16")	66,0 (2,6")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-280	14,2 (9/16")	71,1 (2,8")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-300	14,2 (9/16")	76,2 (3")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-320	14,2 (9/16")	81,3 (3,2")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-340	14,2 (9/16")	86,4 (3,4")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-360	14,2 (9/16")	91,4 (3,6")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-380	14,2 (9/16")	96,5 (3,8")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-400	14,2 (9/16")	101,6 (4")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-420	14,2 (9/16")	106,7 (4,2")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-440	14,2 (9/16")	111,8 (4,4")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-460	14,2 (9/16")	116,8 (4,6")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-480	14,2 (9/16")	121,9 (4,8")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-500	14,2 (9/16")	127,0 (5")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-520	14,2 (9/16")	132,1 (5,2")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-540	14,2 (9/16")	137,2 (5,4")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-560	14,2 (9/16")	142,2 (5,6")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-580	14,2 (9/16")	147,3 (5,8")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-600	14,2 (9/16")	152,4 (6")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-620	14,2 (9/16")	157,5 (6,2")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-640	14,2 (9/16")	162,6 (6,4")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-660	14,2 (9/16")	167,6 (6,6")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6



Order No.	d ₁ +0.00 -0.08	l ₁ grip +1.50 -0.00	d ₂	d ₃	l ₂	l ₃	Pull out strength kg	Single shear strength kN min.
P1250.056-680	14,2 (9/16")	172,7 (6,8")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.056-700	14,2 (9/16")	177,8 (7")	16.3	31.7	17.4	7.92	5,45 - 6,81	97.6
P1250.062-110	15,8 (5/8")	27,9 (1,1")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-130	15,8 (5/8")	33,0 (1,3")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-150	15,8 (5/8")	38,1 (1,5")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-160	15,8 (5/8")	40,6 (1,6")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-170	15,8 (5/8")	43,2 (1,7")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-190	15,8 (5/8")	48,3 (1,9")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-210	15,8 (5/8")	53,3 (2,1")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-230	15,8 (5/8")	58,4 (2,3")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-250	15,8 (5/8")	63,5 (2,5")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-270	15,8 (5/8")	68,6 (2,7")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-290	15,8 (5/8")	73,7 (2,9")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-310	15,8 (5/8")	78,7 (3,1")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-330	15,8 (5/8")	83,8 (3,3")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-350	15,8 (5/8")	88,9 (3,5")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-370	15,8 (5/8")	94,0 (3,7")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-390	15,8 (5/8")	99,1 (3,9")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-410	15,8 (5/8")	104,1 (4,1")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-430	15,8 (5/8")	109,2 (4,3")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-450	15,8 (5/8")	114,3 (4,5")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-470	15,8 (5/8")	119,4 (4,7")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-490	15,8 (5/8")	124,5 (4,9")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-510	15,8 (5/8")	129,5 (5,1")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-530	15,8 (5/8")	134,6 (5,3")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-550	15,8 (5/8")	139,7 (5,5")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-570	15,8 (5/8")	144,8 (5,7")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-590	15,8 (5/8")	149,9 (5,9")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-610	15,8 (5/8")	154,9 (6,1")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-630	15,8 (5/8")	160,0 (6,3")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-650	15,8 (5/8")	165,1 (6,5")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-670	15,8 (5/8")	170,2 (6,7")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-690	15,8 (5/8")	175,3 (6,9")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-710	15,8 (5/8")	180,3 (7,1")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-730	15,8 (5/8")	185,4 (7,3")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-750	15,8 (5/8")	190,5 (7,5")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-770	15,8 (5/8")	195,6 (7,7")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.062-790	15,8 (5/8")	200,7 (7,9")	18.0	31.7	19.0	9.52	3,36 - 7,26	121.6
P1250.075-100	19,0 (3/4")	25,4 (1")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-120	19,0 (3/4")	30,5 (1,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-140	19,0 (3/4")	35,6 (1,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-160	19,0 (3/4")	40,6 (1,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-180	19,0 (3/4")	45,7 (1,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-200	19,0 (3/4")	50,8 (2")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-220	19,0 (3/4")	55,9 (2,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-240	19,0 (3/4")	61,0 (2,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-260	19,0 (3/4")	66,0 (2,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-280	19,0 (3/4")	71,1 (2,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-300	19,0 (3/4")	76,2 (3")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-320	19,0 (3/4")	81,3 (3,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-340	19,0 (3/4")	86,4 (3,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-360	19,0 (3/4")	91,4 (3,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-380	19,0 (3/4")	96,5 (3,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-400	19,0 (3/4")	101,6 (4")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-420	19,0 (3/4")	106,7 (4,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-440	19,0 (3/4")	111,8 (4,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-460	19,0 (3/4")	116,8 (4,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-480	19,0 (3/4")	121,9 (4,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-500	19,0 (3/4")	127,0 (5")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-520	19,0 (3/4")	132,1 (5,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-540	19,0 (3/4")	137,2 (5,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-560	19,0 (3/4")	142,2 (5,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-580	19,0 (3/4")	147,3 (5,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-600	19,0 (3/4")	152,4 (6")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-620	19,0 (3/4")	157,5 (6,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-640	19,0 (3/4")	162,6 (6,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-660	19,0 (3/4")	167,6 (6,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6




Detent Pin Steel



Order No.	d ₁ +0.00 -0.08	l ₁ grip +1.50 -0.00	d ₂	d ₃	l ₂	l ₃	Pull out strength kg	Single shear strength kN min.
P1250.075-680	19,0 (3/4")	172,7 (6,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-700	19,0 (3/4")	177,8 (7")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-720	19,0 (3/4")	182,9 (7,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-740	19,0 (3/4")	188,0 (7,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-760	19,0 (3/4")	193,0 (7,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-780	19,0 (3/4")	198,1 (7,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.075-800	19,0 (3/4")	203,2 (8")	21.7	38.1	23.7	9.52	8,17 - 9,98	173.6
P1250.087-110	22,2 (7/8")	27,9 (1,1")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-130	22,2 (7/8")	33,0 (1,3")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-150	22,2 (7/8")	38,1 (1,5")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-170	22,2 (7/8")	43,2 (1,7")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-190	22,2 (7/8")	48,3 (1,9")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-210	22,2 (7/8")	53,3 (2,1")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-230	22,2 (7/8")	58,4 (2,3")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-250	22,2 (7/8")	63,5 (2,5")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-270	22,2 (7/8")	68,6 (2,7")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-290	22,2 (7/8")	73,7 (2,9")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-310	22,2 (7/8")	78,7 (3,1")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-330	22,2 (7/8")	83,8 (3,3")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-350	22,2 (7/8")	88,9 (3,5")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-370	22,2 (7/8")	94,0 (3,7")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-390	22,2 (7/8")	99,1 (3,9")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-400	22,2 (7/8")	101,6 (4")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-410	22,2 (7/8")	104,1 (4,1")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-430	22,2 (7/8")	109,2 (4,3")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-450	22,2 (7/8")	114,3 (4,5")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-470	22,2 (7/8")	119,4 (4,7")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-490	22,2 (7/8")	124,5 (4,9")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-510	22,2 (7/8")	129,5 (5,1")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-530	22,2 (7/8")	134,6 (5,3")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-550	22,2 (7/8")	139,7 (5,5")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-570	22,2 (7/8")	144,8 (5,7")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-590	22,2 (7/8")	149,9 (5,9")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-610	22,2 (7/8")	154,9 (6,1")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-630	22,2 (7/8")	160,0 (6,3")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-650	22,2 (7/8")	165,1 (6,5")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-670	22,2 (7/8")	170,2 (6,7")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-690	22,2 (7/8")	175,3 (6,9")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-710	22,2 (7/8")	180,3 (7,1")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-730	22,2 (7/8")	185,4 (7,3")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-750	22,2 (7/8")	190,5 (7,5")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-770	22,2 (7/8")	195,6 (7,7")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.087-790	22,2 (7/8")	200,7 (7,9")	25.2	38.1	25.4	12.7	12,71 - 14,07	239.4
P1250.100-100	25,4 (1")	25,4 (1")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-120	25,4 (1")	30,5 (1,2")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-140	25,4 (1")	35,6 (1,4")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-160	25,4 (1")	40,6 (1,6")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-180	25,4 (1")	45,7 (1,8")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-200	25,4 (1")	50,8 (2")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-220	25,4 (1")	55,9 (2,2")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-240	25,4 (1")	61,0 (2,4")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-260	25,4 (1")	66,0 (2,6")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-280	25,4 (1")	71,1 (2,8")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-300	25,4 (1")	76,2 (3")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-320	25,4 (1")	81,3 (3,2")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-340	25,4 (1")	86,4 (3,4")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-360	25,4 (1")	91,4 (3,6")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-380	25,4 (1")	96,5 (3,8")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-400	25,4 (1")	101,6 (4")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-420	25,4 (1")	106,7 (4,2")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-440	25,4 (1")	111,8 (4,4")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-460	25,4 (1")	116,8 (4,6")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-480	25,4 (1")	121,9 (4,8")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-500	25,4 (1")	127,0 (5")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-520	25,4 (1")	132,1 (5,2")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-540	25,4 (1")	137,2 (5,4")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-560	25,4 (1")	142,2 (5,6")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3

OTHER PINS



Order No.	d_1 +0.00 -0.08	l_1 grip +1.50 -0.00	d_2	d_3	l_2	l_3	Pull out strength kg	Single shear strength kN min.
P1250.100-580	25,4 (1")	147,3 (5,8")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-600	25,4 (1")	152,4 (6")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-620	25,4 (1")	157,5 (6,2")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-640	25,4 (1")	162,6 (6,4")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-660	25,4 (1")	167,6 (6,6")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-680	25,4 (1")	172,7 (6,8")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-700	25,4 (1")	177,8 (7")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-720	25,4 (1")	182,9 (7,2")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-740	25,4 (1")	188,0 (7,4")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-760	25,4 (1")	193,0 (7,6")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-780	25,4 (1")	198,1 (7,8")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3
P1250.100-800	25,4 (1")	203,2 (8")	28.9	38.1	31.7	12.7	15,88 - 18-15	321.3