




Detent Pin Stainless Steel



P1252.2

OTHER PINS

Material

Shaft: Stainless steel, AISI 303.

Ball & Spring: Stainless steel, AISI 316.

Technical Notes

Detent pins are very economical for use in commercial and military equipment.

The solid body with direct spring loaded ball ensures reliable operation.

For locking telescopic tubing, securing bracket assemblies, as anchor clevis fittings, hinge pins etc where frequent removal is necessary.


Hole sizes - commercial drills provide clearance for our standard pins.

Inch dimensions in brackets ().

Tips

Also available on request in A4 (AISI 316) stainless steel, subject to min. quantity.

Order No.	d ₁ +0.00 -0.08	l ₁ grip +1.5 -0.0	d ₂	d ₃	l ₂	l ₃	Pull out strength kg	Single shear strength kN min.
P1252.056-100	14,2 (9/16")	25,4 (1,0")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-110	14,2 (9/16")	27,9 (1,1")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-120	14,2 (9/16")	30,5 (1,2")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-130	14,2 (9/16")	33,0 (1,3")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-140	14,2 (9/16")	35,6 (1,4")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-150	14,2 (9/16")	38,1 (1,5")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-160	14,2 (9/16")	40,6 (1,6")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-170	14,2 (9/16")	43,2 (1,7")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-180	14,2 (9/16")	45,7 (1,8")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-190	14,2 (9/16")	48,3 (1,9")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-200	14,2 (9/16")	50,8 (2,0")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-210	14,2 (9/16")	53,3 (2,1")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-220	14,2 (9/16")	55,9 (2,2")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-230	14,2 (9/16")	58,4 (2,3")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-240	14,2 (9/16")	61,0 (2,4")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-250	14,2 (9/16")	63,5 (2,5")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-260	14,2 (9/16")	66,0 (2,6")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-270	14,2 (9/16")	68,6 (2,7")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-280	14,2 (9/16")	71,1 (2,8")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-290	14,2 (9/16")	73,7 (2,9")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-300	14,2 (9/16")	76,2 (3,0")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-310	14,2 (9/16")	78,7 (3,1")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-320	14,2 (9/16")	81,3 (3,2")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-330	14,2 (9/16")	83,8 (3,3")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-340	14,2 (9/16")	86,4 (3,4")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-350	14,2 (9/16")	88,9 (3,5")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-360	14,2 (9/16")	91,4 (3,6")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-370	14,2 (9/16")	94,0 (3,7")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-380	14,2 (9/16")	96,5 (3,8")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3
P1252.056-390	14,2 (9/16")	99,1 (3,9")	16.3	31.7	17.4	7.92	5,45 - 6,81	110.3



Order No.	d ₁ +0.00 -0.08	l ₁ grip +1.5 -0.0	d ₂	d ₃	l ₂	l ₃	Pull out strength kg	Single shear strength kN min.
P1252.056-400	14,2 (9/16")	101,6 (4,0")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-410	14,2 (9/16")	104,1 (4,1")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-420	14,2 (9/16")	106,7 (4,2")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-430	14,2 (9/16")	109,2 (4,3")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-440	14,2 (9/16")	111,8 (4,4")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-450	14,2 (9/16")	114,3 (4,5")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-460	14,2 (9/16")	116,8 (4,6")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-470	14,2 (9/16")	119,4 (4,7")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-480	14,2 (9/16")	121,9 (4,8")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-490	14,2 (9/16")	124,5 (4,9")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-500	14,2 (9/16")	127,0 (5,0")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-510	14,2 (9/16")	129,5 (5,1")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-520	14,2 (9/16")	132,1 (5,2")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-530	14,2 (9/16")	134,6 (5,3")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-540	14,2 (9/16")	137,2 (5,4")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-550	14,2 (9/16")	139,7 (5,5")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-560	14,2 (9/16")	142,2 (5,6")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-570	14,2 (9/16")	144,8 (5,7")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-580	14,2 (9/16")	147,3 (5,8")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-590	14,2 (9/16")	149,9 (5,9")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-600	14,2 (9/16")	152,4 (6,0")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-610	14,2 (9/16")	154,9 (6,1")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-620	14,2 (9/16")	157,5 (6,2")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-630	14,2 (9/16")	160,0 (6,3")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-640	14,2 (9/16")	162,6 (6,4")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-650	14,2 (9/16")	165,1 (6,5")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-660	14,2 (9/16")	167,6 (6,6")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-670	14,2 (9/16")	170,2 (6,7")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-680	14,2 (9/16")	172,7 (6,8")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-690	14,2 (9/16")	175,3 (6,9")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.056-700	14,2 (9/16")	177,8 (7,0")	16,3	31,7	17,4	7,92	5,45 - 6,81	110,3
P1252.062-100	15,8 (5/8")	25,4 (1,0")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-110	15,8 (5/8")	27,9 (1,1")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-120	15,8 (5/8")	30,5 (1,2")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-130	15,8 (5/8")	33,0 (1,3")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-140	15,8 (5/8")	35,6 (1,4")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-150	15,8 (5/8")	38,1 (1,5")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-160	15,8 (5/8")	40,6 (1,6")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-170	15,8 (5/8")	43,2 (1,7")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-180	15,8 (5/8")	45,7 (1,8")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-190	15,8 (5/8")	48,3 (1,9")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-200	15,8 (5/8")	50,8 (2,0")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-210	15,8 (5/8")	53,3 (2,1")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-220	15,8 (5/8")	55,9 (2,2")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-230	15,8 (5/8")	58,4 (2,3")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-240	15,8 (5/8")	61,0 (2,4")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-250	15,8 (5/8")	63,5 (2,5")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-260	15,8 (5/8")	66,0 (2,6")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-270	15,8 (5/8")	68,6 (2,7")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-280	15,8 (5/8")	71,1 (2,8")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-290	15,8 (5/8")	73,7 (2,9")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-300	15,8 (5/8")	76,2 (3,0")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-310	15,8 (5/8")	78,7 (3,1")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-320	15,8 (5/8")	81,3 (3,2")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-330	15,8 (5/8")	83,8 (3,3")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-340	15,8 (5/8")	86,4 (3,4")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-360	15,8 (5/8")	91,4 (3,6")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-370	15,8 (5/8")	94,0 (3,7")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-380	15,8 (5/8")	96,5 (3,8")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-390	15,8 (5/8")	99,1 (3,9")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-410	15,8 (5/8")	104,1 (4,1")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-420	15,8 (5/8")	106,7 (4,2")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-430	15,8 (5/8")	109,2 (4,3")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-440	15,8 (5/8")	111,8 (4,4")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-450	15,8 (5/8")	114,3 (4,5")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-460	15,8 (5/8")	116,8 (4,6")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3
P1252.062-470	15,8 (5/8")	119,4 (4,7")	18,0	31,7	19,0	9,52	6,36 - 7,26	137,3




Detent Pin Stainless Steel



Order No.	d ₁ +0.00 -0.08	l ₁ grip +1.5 -0.0	d ₂	d ₃	l ₂	l ₃	Pull out strength kg	Single shear strength kN min.
P1252.062-480	15,8 (5/8")	121,9 (4,8")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-490	15,8 (5/8")	124,5 (4,9")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-510	15,8 (5/8")	129,5 (5,1")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-520	15,8 (5/8")	132,1 (5,2")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-530	15,8 (5/8")	134,6 (5,3")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-540	15,8 (5/8")	137,2 (5,4")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-550	15,8 (5/8")	139,7 (5,5")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-560	15,8 (5/8")	142,2 (5,6")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-570	15,8 (5/8")	144,8 (5,7")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-580	15,8 (5/8")	147,3 (5,8")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-590	15,8 (5/8")	149,9 (5,9")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-610	15,8 (5/8")	154,9 (6,1")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-620	15,8 (5/8")	157,5 (6,2")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-630	15,8 (5/8")	160,0 (6,3")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-640	15,8 (5/8")	162,6 (6,4")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-650	15,8 (5/8")	165,1 (6,5")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-660	15,8 (5/8")	167,6 (6,6")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-670	15,8 (5/8")	170,2 (6,7")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-680	15,8 (5/8")	172,7 (6,8")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-690	15,8 (5/8")	175,3 (6,9")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-700	15,8 (5/8")	177,8 (7,0")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-710	15,8 (5/8")	180,3 (7,1")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-720	15,8 (5/8")	182,9 (7,2")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-730	15,8 (5/8")	185,4 (7,3")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-740	15,8 (5/8")	188,0 (7,4")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-750	15,8 (5/8")	190,5 (7,5")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-760	15,8 (5/8")	193,0 (7,6")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-770	15,8 (5/8")	195,6 (7,7")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-780	15,8 (5/8")	198,1 (7,8")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-790	15,8 (5/8")	200,7 (7,9")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.062-800	15,8 (5/8")	203,2 (8,0")	18.0	31.7	19.0	9.52	6,36 - 7,26	137.3
P1252.075-100	19,0 (3/4")	25,4 (1,0")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-110	19,0 (3/4")	27,9 (1,1")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-120	19,0 (3/4")	30,5 (1,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-130	19,0 (3/4")	33,0 (1,3")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-140	19,0 (3/4")	35,6 (1,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-150	19,0 (3/4")	38,1 (1,5")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-160	19,0 (3/4")	40,6 (1,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-170	19,0 (3/4")	43,2 (1,7")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-180	19,0 (3/4")	45,7 (1,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-190	19,0 (3/4")	48,3 (1,9")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-200	19,0 (3/4")	50,8 (2,0")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-210	19,0 (3/4")	53,3 (2,1")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-220	19,0 (3/4")	55,9 (2,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-230	19,0 (3/4")	58,4 (2,3")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-240	19,0 (3/4")	61,0 (2,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-260	19,0 (3/4")	66,0 (2,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-270	19,0 (3/4")	68,6 (2,7")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-280	19,0 (3/4")	71,1 (2,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-290	19,0 (3/4")	73,7 (2,9")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-300	19,0 (3/4")	76,2 (3,0")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-310	19,0 (3/4")	78,7 (3,1")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-320	19,0 (3/4")	81,3 (3,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-330	19,0 (3/4")	83,8 (3,3")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-340	19,0 (3/4")	86,4 (3,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-350	19,0 (3/4")	88,9 (3,5")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-360	19,0 (3/4")	91,4 (3,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-370	19,0 (3/4")	94,0 (3,7")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-380	19,0 (3/4")	96,5 (3,8")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-390	19,0 (3/4")	99,1 (3,9")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-400	19,0 (3/4")	101,6 (4,0")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-410	19,0 (3/4")	104,1 (4,1")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-420	19,0 (3/4")	106,7 (4,2")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-430	19,0 (3/4")	109,2 (4,3")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-440	19,0 (3/4")	111,8 (4,4")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-450	19,0 (3/4")	114,3 (4,5")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9
P1252.075-460	19,0 (3/4")	116,8 (4,6")	21.7	38.1	23.7	9.52	8,17 - 9,98	195.9

OTHER PINS



Order No.	d ₁ +0.00/-0.08	l ₁ grip +1.5/-0.0	d ₂	d ₃	l ₂	l ₃	Pull out strength kg	Single shear strength kN min.
P1252.075-470	19,0 (3/4")	119,4 (4,7")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-480	19,0 (3/4")	121,9 (4,8")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-490	19,0 (3/4")	124,5 (4,9")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-500	19,0 (3/4")	127,0 (5,0")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-510	19,0 (3/4")	129,5 (5,1")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-520	19,0 (3/4")	132,1 (5,2")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-530	19,0 (3/4")	134,6 (5,3")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-540	19,0 (3/4")	137,2 (5,4")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-550	19,0 (3/4")	139,7 (5,5")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-560	19,0 (3/4")	142,2 (5,6")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-570	19,0 (3/4")	144,8 (5,7")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-580	19,0 (3/4")	147,3 (5,8")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-590	19,0 (3/4")	149,9 (5,9")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-600	19,0 (3/4")	152,4 (6,0")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-610	19,0 (3/4")	154,9 (6,1")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-620	19,0 (3/4")	157,5 (6,2")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-630	19,0 (3/4")	160,0 (6,3")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-640	19,0 (3/4")	162,6 (6,4")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-650	19,0 (3/4")	165,1 (6,5")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-660	19,0 (3/4")	167,6 (6,6")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-670	19,0 (3/4")	170,2 (6,7")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-680	19,0 (3/4")	172,7 (6,8")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-690	19,0 (3/4")	175,3 (6,9")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-700	19,0 (3/4")	177,8 (7,0")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-710	19,0 (3/4")	180,3 (7,1")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-720	19,0 (3/4")	182,9 (7,2")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-730	19,0 (3/4")	185,4 (7,3")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-740	19,0 (3/4")	188,0 (7,4")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-750	19,0 (3/4")	190,5 (7,5")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-760	19,0 (3/4")	193,0 (7,6")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-770	19,0 (3/4")	195,6 (7,7")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-780	19,0 (3/4")	198,1 (7,8")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.075-790	19,0 (3/4")	200,7 (7,9")	21,7	38,1	23,7	9,52	8,17 - 9,98	195,9
P1252.087-100	22,2 (7/8")	25,4 (1,0")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-150	22,2 (7/8")	38,1 (1,5")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-200	22,2 (7/8")	50,8 (2,0")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-250	22,2 (7/8")	63,5 (2,5")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-300	22,2 (7/8")	76,2 (3,0")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-350	22,2 (7/8")	88,9 (3,5")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-400	22,2 (7/8")	101,6 (4,0")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-450	22,2 (7/8")	114,3 (4,5")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-500	22,2 (7/8")	127,0 (5,0")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-550	22,2 (7/8")	139,7 (5,5")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-600	22,2 (7/8")	152,4 (6,0")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-650	22,2 (7/8")	165,1 (6,5")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-700	22,2 (7/8")	177,8 (7,0")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.087-800	22,2 (7/8")	203,2 (8,0")	25,2	38,1	25,4	12,7	12,71 - 14,07	262,4
P1252.100-100	25,4 (1")	25,4 (1,0")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-110	25,4 (1")	27,9 (1,1")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-120	25,4 (1")	30,5 (1,2")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-130	25,4 (1")	33,0 (1,3")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-140	25,4 (1")	35,6 (1,4")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-150	25,4 (1")	38,1 (1,5")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-160	25,4 (1")	40,6 (1,6")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-170	25,4 (1")	43,2 (1,7")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-180	25,4 (1")	45,7 (1,8")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-190	25,4 (1")	48,3 (1,9")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-200	25,4 (1")	50,8 (2,0")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-210	25,4 (1")	53,3 (2,1")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-220	25,4 (1")	55,9 (2,2")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-230	25,4 (1")	58,4 (2,3")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-240	25,4 (1")	61,0 (2,4")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-250	25,4 (1")	63,5 (2,5")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-260	25,4 (1")	66,0 (2,6")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-270	25,4 (1")	68,6 (2,7")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-280	25,4 (1")	71,1 (2,8")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0
P1252.100-290	25,4 (1")	73,7 (2,9")	28,9	38,1	31,7	12,7	15,88 - 18,15	353,0



Detent Pin Stainless Steel



Other Pins

Order No.	d ₁ +0.00 -0.08	l ₁ grip +1.5 -0.0	d ₂	d ₃	l ₂	l ₃	Pull out strength kg	Single shear strength kN min.
P1252.100-300	25,4 (1")	76,2 (3,0")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-310	25,4 (1")	78,7 (3,1")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-320	25,4 (1")	81,3 (3,2")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-330	25,4 (1")	83,8 (3,3")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-340	25,4 (1")	86,4 (3,4")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-350	25,4 (1")	88,9 (3,5")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-360	25,4 (1")	91,4 (3,6")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-370	25,4 (1")	94,0 (3,7")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-380	25,4 (1")	96,5 (3,8")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-390	25,4 (1")	99,1 (3,9")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-400	25,4 (1")	101,6 (4,0")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-410	25,4 (1")	104,1 (4,1")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-420	25,4 (1")	106,7 (4,2")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-430	25,4 (1")	109,2 (4,3")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-440	25,4 (1")	111,8 (4,4")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-450	25,4 (1")	114,3 (4,5")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-460	25,4 (1")	116,8 (4,6")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-470	25,4 (1")	119,4 (4,7")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-480	25,4 (1")	121,9 (4,8")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-490	25,4 (1")	124,5 (4,9")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-500	25,4 (1")	127,0 (5,0")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-510	25,4 (1")	129,5 (5,1")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-520	25,4 (1")	132,1 (5,2")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-530	25,4 (1")	134,6 (5,3")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-540	25,4 (1")	137,2 (5,4")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-550	25,4 (1")	139,7 (5,5")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-560	25,4 (1")	142,2 (5,6")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-570	25,4 (1")	144,8 (5,7")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-580	25,4 (1")	147,3 (5,8")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-590	25,4 (1")	149,9 (5,9")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-600	25,4 (1")	152,4 (6,0")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-610	25,4 (1")	154,9 (6,1")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-620	25,4 (1")	157,5 (6,2")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-630	25,4 (1")	160,0 (6,3")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-640	25,4 (1")	162,6 (6,4")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-650	25,4 (1")	165,1 (6,5")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-660	25,4 (1")	167,6 (6,6")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-670	25,4 (1")	170,2 (6,7")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-680	25,4 (1")	172,7 (6,8")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-690	25,4 (1")	175,3 (6,9")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-700	25,4 (1")	177,8 (7,0")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-710	25,4 (1")	180,3 (7,1")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-720	25,4 (1")	182,9 (7,2")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-730	25,4 (1")	185,4 (7,3")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-740	25,4 (1")	188,0 (7,4")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-750	25,4 (1")	190,5 (7,5")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-760	25,4 (1")	193,0 (7,6")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-770	25,4 (1")	195,6 (7,7")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-780	25,4 (1")	198,1 (7,8")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-790	25,4 (1")	200,7 (7,9")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0
P1252.100-800	25,4 (1")	203,2 (8,0")	28.9	38.1	31.7	12.7	15,88 - 18,15	353.0

OTHER PINS