



Metric Ultra Low Slotted Cap Head


stainless steel 303

Standard Screws



P0204.A2

STANDARD SCREWS



Material

Stainless Steel AISI 303


Important Notes

Manufactured from AISI Stainless Steel (Grade 303), these screws offer excellent corrosion resistance and reliable perfor-

mance in a wide range of environments. The slotted drive allows for easy installation and removal using standard tools, while the ultra-low cap head is specifically designed to reduce protrusion and prevent interference in assemblies with limited

clearance. This makes them ideal for applications requiring flush or near-flush finishes. The high-quality stainless steel construction ensures strong, secure fastening even in demanding conditions.

Order No.	d ₁	l ₁	d ₂	l ₂	d ₃	l ₃
P0204.030-005-A2	M 3	5	3.8	1.0	5.5	1.0
P0204.030-006-A2	M 3	6	3.8	1.0	5.5	1.0
P0204.030-008-A2	M 3	8	3.8	1.0	5.5	1.0
P0204.030-010-A2	M 3	10	3.8	1.0	5.5	1.0
P0204.030-012-A2	M 3	12	3.8	1.0	5.5	1.0
P0204.030-016-A2	M 3	16	3.8	1.0	5.5	1.0
P0204.040-006-A2	M 4	6	4.5	1.3	7.0	1.3
P0204.040-008-A2	M 4	8	4.5	1.3	7.0	1.3
P0204.040-010-A2	M 4	10	4.5	1.3	7.0	1.3
P0204.040-012-A2	M 4	12	4.5	1.3	7.0	1.3
P0204.040-016-A2	M 4	16	4.5	1.3	7.0	1.3
P0204.040-020-A2	M 4	20	4.5	1.3	7.0	1.3
P0204.040-025-A2	M 4	25	4.5	1.3	7.0	1.3
P0204.040-030-A2	M 4	30	4.5	1.3	7.0	1.3
P0204.040-040-A2	M 4	40	4.5	1.3	7.0	1.3
P0204.050-006-A2	M 5	6	5.2	1.7	8.5	1.7
P0204.050-008-A2	M 5	8	5.2	1.7	8.5	1.7
P0204.050-010-A2	M 5	10	5.2	1.7	8.5	1.7
P0204.050-012-A2	M 5	12	5.2	1.7	8.5	1.7
P0204.050-016-A2	M 5	16	5.2	1.7	8.5	1.7
P0204.050-020-A2	M 5	20	5.2	1.7	8.5	1.7
P0204.050-025-A2	M 5	25	5.2	1.7	8.5	1.7
P0204.050-030-A2	M 5	30	5.2	1.7	8.5	1.7
P0204.050-040-A2	M 5	40	5.2	1.7	8.5	1.7
P0204.050-050-A2	M 5	50	5.2	1.7	8.5	1.7
P0204.060-008-A2	M 6	8	6.3	2.0	10.0	2.0
P0204.060-010-A2	M 6	10	6.3	2.0	10.0	2.0
P0204.060-012-A2	M 6	12	6.3	2.0	10.0	2.0
P0204.060-016-A2	M 6	16	6.3	2.0	10.0	2.0
P0204.060-020-A2	M 6	20	6.3	2.0	10.0	2.0
P0204.060-025-A2	M 6	25	6.3	2.0	10.0	2.0
P0204.060-030-A2	M 6	30	6.3	2.0	10.0	2.0



Order No.	d ₁	l ₁	d ₂	l ₂	d ₃	l ₃
P0204.060-040-A2	M 6	40	6.3	2.0	10.0	2.0
P0204.060-050-A2	M 6	50	6.3	2.0	10.0	2.0
P0204.080-010-A2	M 8	10	7.5	2.7	13.0	2.7
P0204.080-012-A2	M 8	12	7.5	2.7	13.0	2.7
P0204.080-016-A2	M 8	16	7.5	2.7	13.0	2.7
P0204.080-020-A2	M 8	20	7.5	2.7	13.0	2.7
P0204.080-025-A2	M 8	25	7.5	2.7	13.0	2.7
P0204.080-030-A2	M 8	30	7.5	2.7	13.0	2.7
P0204.080-040-A2	M 8	40	7.5	2.7	13.0	2.7
P0204.080-050-A2	M 8	50	7.5	2.7	13.0	2.7
P0204.080-060-A2	M 8	60	7.5	2.7	13.0	2.7
P0204.010-012-A2	M10	12	9.3	3.3	16.0	3.3
P0204.010-016-A2	M10	16	9.3	3.3	16.0	3.3
P0204.010-020-A2	M10	20	9.3	3.3	16.0	3.3
P0204.010-025-A2	M10	25	9.3	3.3	16.0	3.3
P0204.010-030-A2	M10	30	9.3	3.3	16.0	3.3
P0204.010-040-A2	M10	40	9.3	3.3	16.0	3.3
P0204.010-060-A2	M10	60	9.3	3.3	16.0	3.3
P0204.010-050-A2	M10	50	9.3	3.3	16.0	3.3