




Anti-vibration Fail-Safe Mounts steel

Steel

Anti-Vibration Components



P2100.AV

ANTI-VIBRATION COMPONENTS

Material

Rubber on silver zinc plated steel (rubber hardness - 45-75 Shore A).

Technical Notes

These mounts control vibration in three axes.

Primarily used for marine applications, engines, compressors, pumps, generators

etc.

Fitted with a mechanical fail-safe stop. They are very robust to cope with high start/stop forces and vibrations from marine and other engines.

For stainless steel versions please see part nos. P2101 and P2102. Stud and nuts on

request.

Tips

These are a very popular anti-vibration mount for light to heavy duty applications. Take the total weight of the load to be supported, divide it by the number of mounts to be used and select an appropriate mount from the table.

Order No.	d ₁	d ₂	l ₁	l ₂	w ₁	d ₃	d ₄	h ₁	h ₂	Load kg max.
P2100.060-045	60	M12	100	120	60	11	14	40	95	50
P2100.060-055	60	M12	100	120	60	11	14	40	95	65
P2100.060-065	60	M12	100	120	60	11	14	40	95	100
P2100.075-045	75	M16	140	183	75	13	20	50	110	150
P2100.075-055	75	M16	140	183	75	13	20	50	110	200
P2100.075-065	75	M16	140	183	75	13	20	50	110	300
P2100.075-075	75	M16	140	183	75	13	20	50	110	550
P2100.080-065	80	M20	182	230	112	18	25	70	110	750



Automotion
AN ESSENTIA COMPANY

0333 207 4498

sales@automotioncomponents.co.uk



Recommendations for machine mounts

Machine mounts should be installed between two parallel and perfectly flat surfaces. Mounts operating tilted or twisted do not work properly. This may be due to incorrect alignment, tolerances in the building of the structure or over-tightened torque during the installation of the anti-vibration mounts.



incorrect ✗



correct ✓



incorrect ✗



correct ✓



incorrect ✗



correct ✓



incorrect ✗



correct ✓



incorrect ✗



correct ✓