




Precision Adjuster with locking nut

Levelling Feet



P2183

LEVELLING FEET

Material

Steel (type 42 CrMo4 V, 1.7225) zinc plated or stainless steel A1 (A4 on request).

Technical Notes

After setting the height, the structure can be bolted down using a suitable 8,8

strength bolt.

The net load that the unit can carry is the maximum load less the tightening torque recommended for the bolt.

Designed for applications with a dynamic load, or where no fasteners are used. The

locknut enables locking of the adjuster in a pre-set position.

Order No.	Material	For bolt	h ₁	h ₂	h ₃	d ₁	d ₂	d ₃	Load with bolt kN max.	Load w/o bolt kN max.
P2183.043-060-ZP	Steel	M 6	43	33	10	25	6.6	M15x1,0	30.70	40.00
P2183.055-060-ZP	Steel	M 6	55	41	14	32	6.6	M20x1,0	55.70	65.00
P2183.055-080-ZP	Steel	M 8	55	41	14	32	9.0	M20x1,0	48.00	65.00
P2183.067-100-ZP	Steel	M10	67	49	18	45	11.0	M30x1,5	92.90	120.00
P2183.067-120-ZP	Steel	M12	67	49	18	45	13.5	M30x1,5	80.40	120.00
P2183.067-160-ZP	Steel	M16	67	49	18	45	17.5	M30x1,5	45.50	120.00
P2183.086-160-ZP	Steel	M16	86	63	23	58	17.5	M40x1,5	136.00	210.00
P2183.086-200-ZP	Steel	M20	86	63	23	58	22.0	M40x1,5	90.00	210.00
P2183.086-240-ZP	Steel	M24	86	63	23	58	26.0	M40x1,5	37.00	210.00
P2183.106-200-ZP	Steel	M20	106	77	29	70	22.0	M50x1,5	210.00	330.00
P2183.106-240-ZP	Steel	M24	106	77	29	70	26.0	M50x1,5	157.00	330.00
P2183.106-300-ZP	Steel	M30	106	77	29	70	33.0	M50x1,5	53.00	330.00
P2183.043-060-A2	Stainless steel	M 6	43	33	10	25	6.6	M15x1,0	20.26	27.10
P2183.055-060-A2	Stainless steel	M 6	55	41	14	32	6.6	M20x1,0	36.56	43.40
P2183.055-080-A2	Stainless steel	M 8	55	41	14	32	9.0	M20x1,0	30.86	43.40
P2183.055-100-A2	Stainless steel	M10	55	41	14	32	11.0	M20x1,0	23.41	43.40
P2183.067-120-A2	Stainless steel	M12	67	49	18	45	13.5	M30x1,5	54.82	84.00
P2183.067-160-A2	Stainless steel	M16	67	49	18	45	17.5	M30x1,5	28.90	84.00
P2183.086-160-A2	Stainless steel	M16	86	63	23	58	17.5	M40x1,5	92.90	148.00
P2183.086-200-A2	Stainless steel	M20	86	63	23	58	22.0	M40x1,5	59.08	148.00
P2183.086-240-A2	Stainless steel	M24	86	63	23	58	26.0	M40x1,5	20.30	148.00
P2183.106-200-A2	Stainless steel	M20	106	77	29	70	22.0	M50x1,5	136.08	225.00
P2183.106-240-A2	Stainless steel	M24	106	77	29	70	26.0	M50x1,5	97.30	225.00
P2183.106-300-A2	Stainless steel	M30	106	77	29	70	33.0	M50x1,5	20.60	225.00

Levelling Feet

Precision Adjuster
with locking nut



LEVELLING FEET

