




Levelling Feet

bolt down option, bolt stainless steel



Levelling Feet



P2203.2

LEVELLING FEET

Material

Pad: polyamide reinforced by fibre glass with anti-slip pad.
Bolt: stainless steel AISI 304.

Technical Notes

Load values refer to static loads, located at half the screw height.
When vibrations or dynamic loads are


present these values should be reduced.
Larger pad size allows for bolt down holes to be drilled through.

Order No.	d ₁	l ₁	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	A/F	Load kN max.
P2203.083-10-050	M10	50	83	8.5	55	91	38	27	14	15
P2203.083-10-075	M10	75	83	8.5	55	116	38	27	14	15
P2203.083-10-100	M10	100	83	8.5	55	141	38	27	14	15
P2203.083-10-125	M10	125	83	8.5	55	166	38	27	14	15
P2203.083-12-050	M12	50	83	8.5	55	91	38	27	14	15
P2203.083-12-075	M12	75	83	8.5	55	116	38	27	14	15
P2203.083-12-100	M12	100	83	8.5	55	141	38	27	14	15
P2203.083-12-125	M12	125	83	8.5	55	166	38	27	14	15
P2203.083-14-050	M14	50	83	8.5	55	91	38	27	14	20
P2203.083-14-075	M14	75	83	8.5	55	116	38	27	14	20
P2203.083-14-100	M14	100	83	8.5	55	141	38	27	14	20
P2203.083-14-125	M14	125	83	8.5	55	166	38	27	14	20
P2203.083-14-150	M14	150	83	8.5	55	191	38	27	14	20
P2203.083-14-175	M14	175	83	8.5	55	216	38	27	14	20
P2203.083-16-050	M16	50	83	8.5	55	94	41	27	13	20
P2203.083-16-075	M16	75	83	8.5	55	119	41	27	13	20
P2203.083-16-100	M16	100	83	8.5	55	144	41	27	13	20
P2203.083-16-125	M16	125	83	8.5	55	169	41	27	13	20
P2203.083-16-150	M16	150	83	8.5	55	194	41	27	13	20
P2203.083-16-175	M16	175	83	8.5	55	219	41	27	13	20
P2203.083-16-200	M16	200	83	8.5	55	244	41	27	13	20
P2203.103-16-050	M16	50	103	12.5	73	104	51	32	20	25
P2203.103-16-075	M16	75	103	12.5	73	129	51	32	20	25
P2203.103-16-100	M16	100	103	12.5	73	154	51	32	20	25
P2203.103-16-125	M16	125	103	12.5	73	179	51	32	20	25
P2203.103-16-150	M16	150	103	12.5	73	204	51	32	20	25
P2203.103-16-175	M16	175	103	12.5	73	229	51	32	20	25
P2203.103-16-200	M16	200	103	12.5	73	254	51	32	20	25
P2203.103-16-225	M16	225	103	12.5	73	279	51	32	20	25
P2203.083-20-075	M20	75	83	8.5	55	119	41	27	17	20
P2203.083-20-100	M20	100	83	8.5	55	144	41	27	17	20
P2203.083-20-125	M20	125	83	8.5	55	169	41	27	17	20
P2203.083-20-150	M20	150	83	8.5	55	194	41	27	17	20

Levelling Feet

Levelling Feet

bolt down option, bolt **stainless steel**





LEVELLING FEET

Order No.	d ₁	l ₁	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	A/F	Load kN max.
P2203.083-20-175	M20	175	83	8.5	55	219	41	27	17	20
P2203.083-20-200	M20	200	83	8.5	55	244	41	27	17	20
P2203.083-20-225	M20	225	83	8.5	55	269	41	27	17	20
P2203.103-20-100	M20	100	103	12.5	73	154	51	32	20	25
P2203.103-20-125	M20	125	103	12.5	73	179	51	32	20	25
P2203.103-20-150	M20	150	103	12.5	73	204	51	32	20	25
P2203.103-20-175	M20	175	103	12.5	73	229	51	32	20	25
P2203.103-20-200	M20	200	103	12.5	73	254	51	32	20	25
P2203.103-20-225	M20	225	103	12.5	73	279	51	32	20	25
P2203.103-24-075	M24	75	103	12.5	73	129	51	32	20	25
P2203.103-24-100	M24	100	103	12.5	73	154	51	32	20	25
P2203.103-24-125	M24	125	103	12.5	73	179	51	32	20	25
P2203.103-24-150	M24	150	103	12.5	73	204	51	32	20	25
P2203.103-24-175	M24	175	103	12.5	73	229	51	32	20	25
P2203.103-24-200	M24	200	103	12.5	73	280	51	32	20	25
P2203.103-24-225	M24	250	103	12.5	73	302	51	32	20	25



All levelling feet can be produced with the following fixing types:



Thread versions

- Metric thread - coarse pitch (standard)
- Metric thread - fine pitch
- Thread gas 55°
- Imperial thread Unc
- Whitworth thread

* For non-standard threads a minimum order will apply.

Levelling Feet from Automotion Components

LEVELLING FEET