




Reduced C'snk Head Insert Nuts

Reduced - steel, zinc-plated

Insert Nuts



P0824.ZP

INSERT NUTS

Material

Steel, zinc-plated.

The knurled body provides extra turning

resistance.

Technical Notes

Knurled body type, plain available on request.

Provides near flush installation in thin materials.

Tips

Also known as blind rivet nuts or grip nuts.

Important Notes

Reduced height head.

M3-M8: 0<0.7

Order No.	d ₁	Grip range	d ₂ +0 -0.2	d ₃	h ₁	l ₁
P0824.030-020-ZP	M 3	0,5-2,0	4.9	6.0	0.5	9.0
P0824.040-025-ZP	M 4	0,5-2,5	5.9	6.7	0.5	11.3
P0824.040-040-ZP	M 4	2,0-4,0	5.9	7.0	0.5	13.0
P0824.050-030-ZP	M 5	0,5-3,0	6.9	8.0	0.5	12.0
P0824.050-040-ZP	M 5	2,0-4,0	6.9	8.0	0.5	13.0
P0824.060-030-ZP	M 6	0,5-3,0	8.9	10.0	0.6	14.0
P0824.060-045-ZP	M 6	2,5-4,5	8.9	10.0	0.6	16.0
P0824.080-038-ZP	M 8	0,5-3,8	10.9	12.0	0.6	17.3
P0824.080-050-ZP	M 8	3,0-5,0	10.9	12.0	0.6	18.5
P0824.100-035-ZP	M10	0,7-3,5	11.9	13.0	0.7	20.0
P0824.100-035A-ZP	M10	0,7-3,5	12.9	14.0	0.8	21.0
P0824.100-060-ZP	M10	3,5-6,0	12.9	14.0	0.8	22.0
P0824.120-035-ZP	M12	1,0-3,5	15.9	17.0	1.0	24.2