





Timing Belts- 9,525mm circular pitch 12,7mm wide

Chains, Belts & Pulleys



R1410

CHAINS, BELTS & PULLEYS

Material

Polyurethane (blue) 90A durometer, Ø1,2mm stainless steel cable. Fibre cable core (aramid) also available (particularly suitable for reverse bend applications).

Technical Notes

No flanges required, infinite lengths, silent

drive, no-walk feature.
No lubrication, compact design, positive drive, light weight, extra strong.
Weight: 38 grams/metre.
Ultimate tensile strength 556N.
Temperature range +82°C to -26°C, recommended operating load 53N.
Recommended max. operating speed

1,91m/s.
* Splices are factory overmolded.


Tips

Field splice kit available (37TB-7).

Important Notes

Operates with R1411 belts.

Order No.	No. of pitches	Length ref.
R1410.020	20	190.5
R1410.022	22	209.5
R1410.024	24	228.6
R1410.026	26	247.6
R1410.028	28	266.7
R1410.030	30	285.7
R1410.033	33	314.3
R1410.036	36	342.9
R1410.040	40	381.0
R1410.045	45	428.6
R1410.050	50	476.2
R1410.056	56	533.4
R1410.060	60	571.5
R1410.064	64	609.6
R1410.068	68	647.7
R1410.072	72	685.8
R1410.080	80	765.0
R1410.086	86	819.1
R1410.092	92	876.3
R1410.098	98	933.4
R1410.100	100	952.5
R1410.104	104	990.6
R1410.108	108	1028.7
R1410.112	112	1066.8
R1410.116	116	1104.9
R1410.120	120	1143.0
R1410.124	124	1181.1
R1410.128	128	1219.2
R1410.132	132	1257.3



Order No.	No. of pitches	Length ref.
R1410.136	136	1295.4
R1410.140	140	1333.5
R1410.144	144	1371.6
R1410.148	148	1409.7
R1410.152	152	1447.8
R1410.156	156	1485.9
R1410.160	160	1524.0
R1410.176	176	1676.4
R1410-1.5M	-	1,5 metres not spliced
R1410-3.0M	-	3,0 metres not spliced
R1410-7.5M	-	7,5 metres not spliced
R1410-15M	-	15,0 metres not spliced
R1410-30M	-	30,0 metres not spliced