




1,5/0,25 Module Precision Racks

stainless

Other Precision
Gears



R2172

OTHER PRECISION GEARS

Material

Stainless steel (DIN 1,4005).

Technical Notes

20° pressure angle.
Quality class Din 7/AGMA 10.

Order No.	Module	Linear pitch	a	f	b	h +0.00 -0.13	P ref.	Ø Drill	Tap
R1M-1	1.5	4.71	282.7	9.0	7.9	18.42	16.91	7.0	M 5 X 0,8
R1M-2	1.25	3.93	282.8	9.0	7.9	18.42	17.17	7.0	M 5 X 0,8
R1M-3	1.0	3.14	279.6	5.8	5.5	12.07	11.07	3.8	M 4 X 0,7
R1M-4	0.8	2.51	281.5	5.8	5.5	12.07	11.26	3.8	M 4 X 0,7
R1M-5	0.6	1.88	280.9	5.8	5.5	12.07	11.47	3.8	M 4 X 0,7
R1M-6	0.5	1.57	279.6	5.8	5.5	12.07	11.56	3.8	M 4 X 0,7
R1M-7	0.4	1.26	280.2	5.8	5.5	12.07	11.66	3.8	M 4 X 0,7
R1M-8	0.3	0.94	280.9	4.2	4.0	8.89	8.59	3.1	M 3 X 0,5
R1M-9	0.25	0.78	279.6	4.2	4.0	8.89	8.64	3.1	M 3 X 0,5