




P2080

Material

Rubber on silver zinc plated steel.

Technical Notes

Static load relates to the load the unit can

withstand under compression.

Used where axial and radial loads are present. For frequencies higher than 20Hz.

Order No.	d ₁	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	Static load N max.
P2080.036	36	8.5	18	12	14	10	4	100
P2080.037	36	16.5	20	16.5	11.5	8.5	3	120
P2080.050	50	16.5	23	20	22	13.5	8.5	150
P2080.051	50	28	34	28	18	10.5	7.5	100
P2080.055	55	24	31	28	15	11.5	3.5	175
P2080.060	60	20.5	27	24	22	13	9	240
P2080.075	75	24.5	33	29.5	27	20	8	300