



Right Angle Gear Boxes



RIGHT ANGLE GEAR BOXES



See technical pages for gear box selection guide, based on motor rating, gearing ratio, load type and expected hourly usage hours.

Order No.	Shaft dia. tol. f7	Ratio	Input shaft A kW max.	Output shaft B Nm max.	Output shaft C Nm max.	Weight kg
R2334.1	24	1:1	6.7	25.0	25.0	4.40
R2334.2	24	2:1	4.1	14.0	14.0	4.40
R2334.3	24	3:1	2.2	10.5	10.5	4.40