





Anti vibration Mounts v shaped v shaped

Anti-Vibration Components



P2107

ANTI-VIBRATION COMPONENTS

Material

Rubber on silver zinc plated steel
(rubber hardness 45-65 Shore A).

and one to the piece of equipment. Very good as a shock/isolating mount for oscillations higher than 15Hz.

and air conditioning units from the wall.

Technical Notes

Has a three point anchorage, two to a base

Tips

Can be used to hang compressors, speakers

Order No.	Shore hardness	d ₁	Compression max.	h ₁	h ₂	l ₁	w ₁	l ₂	Axial load kgf max.	Radial load kgf max.
P2107.045	45	12	2.5	35	3	90	73	112	60	60
P2107.055	55	12	3.5	35	3	90	73	112	65	65
P2107.065	65	12	6.0	35	3	90	73	112	70	70



Recommendations for machine mounts

Machine mounts should be installed between two parallel and perfectly flat surfaces. Mounts operating tilted or twisted do not work properly. This may be due to incorrect alignment, tolerances in the building of the structure or over-tightened torque during the installation of the anti-vibration mounts.



incorrect ✗



correct ✓



incorrect ✗



correct ✓



incorrect ✗



correct ✓



incorrect ✗



correct ✓



incorrect ✗



correct ✓