




P2151

LEVELLING FEET

Material

Steel body with zinc plated thread.
Synthetic rubber base (65 Shore A), with anti-slide cavity.

Technical Notes

Suitable for medium and high frequency

vibrations and with smooth floors.

Tips

For inclined floors use the swivel base versions (M12 and M16).
The swivel base versions have a separate screw which rests in the concave cup on the

top portion of the foot body.

Order No.	Style	d ₁	h ₁	d ₂	l ₁	Load range kgf
P2151.040-F	Fixed	40	15	M 8	40	0-60
P2151.063-F	Fixed	63	18	M10	83	30-100
P2151.070-F	Fixed	70	22	M12	90	80-150
P2151.090-F	Fixed	90	25	M12	90	100-350
P2151.106-F	Fixed	106	29	M16	110	300-600
P2151.127-F	Fixed	127	33	M16	110	500-900
P2151.150-F	Fixed	150	39	M16	110	800-1500
P2151.170-F	Fixed	170	42	M16	110	1300-2000
P2151.070-S	Swivel	70	22	M12	90	80-150
P2151.090-S	Swivel	90	26	M12	90	100-350
P2151.106-S	Swivel	106	32	M16	110	300-600
P2151.127-S	Swivel	127	33	M16	110	500-900
P2151.150-S	Swivel	150	39	M16	110	800-1500
P2151.170-S	Swivel	170	42	M16	110	1300-2000