




# Heavy Duty Machine Mounts

## Levelling Feet



**P2153**

LEVELLING FEET

### Material

Coated steel body with special bowl shape to protect against corrosion. Synthetic rubber base (75 Shore A).

### Technical Notes

Provides long life and outstanding stability.

Great adherence to the floor, due to excellent grip property. Quick and easy to install - for machine levelling.

### Tips

Suitable for heavy machinery with strong vibration/impact such as plastic injection

moulding machines, presses, guillotines etc.

Order No.	Type	d <sub>1</sub>	h <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>	Load range kgf
P2153.050	Type 1	50	24	M 8	40	0-100
P2153.075	Type 1	75	35	M10	65	100-350
P2153.085	Type 2	85	40	M12	80	350-600
P2153.090	Type 2	90	49	M16	100	600-900
P2153.125	Type 2	125	52	M16	115	1000-2500
P2153.170	Type 2	170	57	M20	110	2500-4000

