




Tilt Head Precision Adjuster



Levelling Feet



P2184

LEVELLING FEET

Material

Steel (type 42 CrMo4 V, 1.7225) zinc plated or stainless steel A1 (A4 on request).

Technical Notes

After setting the height, the structure can be bolted down using a suitable 8,8

strength bolt.

The net load that the unit can carry is the maximum load less the tightening torque recommended for the bolt. Designed for applications where a wide adjustment range is required - height adjustment is

equal to 15 to 40mm.

Order No.	Material	For bolt	h ₁ min.	h ₂ max.	d ₁	d ₂	d ₃	α app.	Load with bolt kN max.	Load w/o bolt kN max.
P2184.050-040-ZP	Steel	M 4	50	35	25	4.5	M15x1,0	4°	36.00	40.00
P2184.050-050-ZP	Steel	M 5	50	35	25	5.5	M15x1,0	4°	33.40	40.00
P2184.050-060-ZP	Steel	M 6	50	35	25	6.6	M15x1,0	4°	30.70	40.00
P2184.063-060-ZP	Steel	M 6	63	43	32	6.6	M20x1,0	4°	56.70	65.00
P2184.063-080-ZP	Steel	M 8	63	43	32	9.0	M20x1,0	4°	48.90	65.00
P2184.063-100-ZP	Steel	M10	63	43	32	11.0	M20x1,0	4°	37.90	65.00
P2184.079-100-ZP	Steel	M10	79	54	45	11.0	M30x1,5	4°	92.90	120.00
P2184.079-120-ZP	Steel	M12	79	54	45	13.5	M30x1,5	4°	80.40	120.00
P2184.079-160-ZP	Steel	M16	79	54	45	17.5	M30x1,5	4°	45.50	120.00
P2184.102-160-ZP	Steel	M16	102	70	58	17.5	M40x1,5	4°	136.00	210.00
P2184.102-200-ZP	Steel	M20	102	70	58	22.0	M40x1,5	4°	90.80	210.00
P2184.102-240-ZP	Steel	M24	102	70	58	26.0	M40x1,5	4°	37.00	210.00
P2184.123-200-ZP	Steel	M20	123	83	70	22.0	M50x1,5	4°	210.00	330.00
P2184.123-240-ZP	Steel	M24	123	83	70	26.0	M50x1,5	4°	157.00	330.00
P2184.123-300-ZP	Steel	M30	123	83	70	33.0	M50x1,5	4°	53.00	330.00
P2184.050-040-A2	Stainless Steel	M 4	50	35	25	4.5	M15x1,0	4°	24.14	27.10
P2184.050-050-A2	Stainless Steel	M 5	50	35	25	5.5	M15x1,0	4°	22.24	27.10
P2184.050-060-A2	Stainless Steel	M 6	50	35	25	6.6	M15x1,0	4°	20.26	27.10
P2184.063-060-A2	Stainless Steel	M 6	63	43	32	6.6	M20x1,0	4°	36.56	43.40
P2184.063-080-A2	Stainless Steel	M 8	63	43	32	9.0	M20x1,0	4°	30.86	43.40
P2184.063-100-A2	Stainless Steel	M10	63	43	32	11.0	M20x1,0	4°	23.41	43.40
P2184.079-100-A2	Stainless Steel	M10	79	54	45	11.0	M30x1,5	4°	64.01	84.00
P2184.079-120-A2	Stainless Steel	M12	79	54	45	13.5	M30x1,5	4°	54.52	84.00
P2184.079-160-A2	Stainless Steel	M16	79	54	45	17.5	M30x1,5	4°	28.90	84.00
P2184.102-160-A2	Stainless Steel	M16	102	70	58	17.5	M40x1,5	4°	92.90	148.00
P2184.102-200-A2	Stainless Steel	M20	102	70	58	22.0	M40x1,5	4°	59.08	148.00
P2184.102-240-A2	Stainless Steel	M24	102	70	58	26.0	M40x1,5	4°	20.30	148.00
P2184.123-200-A2	Stainless Steel	M20	123	83	70	22.0	M50x1,5	4°	136.08	225.00
P2184.123-240-A2	Stainless Steel	M24	123	83	70	26.0	M50x1,5	4°	97.30	225.00
P2184.123-300-A2	Stainless Steel	M30	123	83	70	33.0	M50x1,5	4°	20.60	225.00