





Bellows Coupling

Aluminium with Phosphor Bronze

Flexible Couplings



R3013

FLEXIBLE COUPLINGS

Material

Mainframe: Anodized aluminium AL 7075
Bellows: Phosphor bronze C5191

tion are individual allowed valure,
so couple reasons of axial offset appearing
at same time would reduce the unit allo-
wable value.

Technical Notes

Offset of angular, parallel or axial devia-

Order No.	d_1 & d_2 tol. h8	d_3	d_4	l_1	l_2	l_3	Clamping screw lock torque Nm
R3013.A-3	3	12	M2,5	23.5	7.5	2.5	0.5
R3013.A-4	4	12	M2,5	23.5	7.5	2.5	0.5
R3013.A-5	5	12	M2,5	23.5	7.5	2.5	0.5
R3013.A-6	6	12	M2,5	23.5	7.5	2.5	0.5
R3013.B-4	4	16	M3	26.5	9	3	0.7
R3013.B-5	5	16	M3	26.5	9	3	0.7
R3013.B-6	6	16	M3	26.5	9	3	0.7
R3013.B-8	8	16	M3	26.5	9	3	0.7
R3013.C-5	5	20	M3	32	10	3.5	0.7
R3013.C-6	6	20	M3	32	10	3.5	0.7
R3013.C-8	8	20	M3	32	10	3.5	0.7
R3013.C-10	10	20	M3	32	10	3.5	0.7
R3013.D-6	6	25	M4	36.5	12	4.5	1.7
R3013.D-8	8	25	M4	36.5	12	4.5	1.7
R3013.D-10	10	25	M4	36.5	12	4.5	1.7
R3013.D-12	12	25	M4	36.5	12	4.5	1.7
R3013.E-6	6	32	M4	42	13.5	5.5	1.7
R3013.E-8	8	32	M4	42	13.5	5.5	1.7
R3013.E-10	10	32	M4	42	13.5	5.5	1.7
R3013.E-12	12	32	M4	42	13.5	5.5	1.7
R3013.E-14	14	32	M4	42	13.5	5.5	1.7