




# Steel Levelling Feet steel

## Levelling Feet



**P2209**

LEVELLING FEET

### Material

Base material: galvanized steel (C40).  
Full Steel base with vulcanized rubber.

half the screw height.

In conditions of vibrations or in presence of dynamic loads these values should be reduced.

### Technical Notes

Load values refer to static loads, located at



| Order No.        | d <sub>1</sub> | d <sub>2</sub> | h <sub>1</sub> | h <sub>2</sub> | h <sub>3</sub> | l <sub>1</sub> | l <sub>2</sub> | A/F | Load<br>kgf<br>max. | Weight<br>g |
|------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----|---------------------|-------------|
| P2209.080-10-050 | 80             | M10            | 85.0           | 35.0           | 25             | 50             | 54             | 14  | 1000                | 292         |
| P2209.080-10-100 | 80             | M10            | 135.0          | 35.0           | 25             | 100            | 54             | 14  | 1000                | 315         |
| P2209.080-12-050 | 80             | M12            | 85.0           | 35.0           | 25             | 50             | 54             | 14  | 1000                | 303         |
| P2209.080-12-100 | 80             | M12            | 135.0          | 35.0           | 25             | 100            | 54             | 14  | 1000                | 335         |
| P2209.080-12-150 | 80             | M12            | 185.0          | 35.0           | 25             | 150            | 54             | 14  | 1000                | 372         |
| P2209.080-14-050 | 80             | M14            | 85.0           | 35.0           | 25             | 50             | 54             | 14  | 1000                | 316         |
| P2209.080-14-100 | 80             | M14            | 135.0          | 35.0           | 25             | 100            | 54             | 14  | 1000                | 363         |
| P2209.080-14-150 | 80             | M14            | 185.0          | 35.0           | 25             | 150            | 54             | 14  | 1000                | 413         |
| P2209.080-16-075 | 80             | M16            | 110.0          | 35.0           | 25             | 75             | 54             | 16  | 1000                | 367         |
| P2209.080-16-100 | 80             | M16            | 135.0          | 35.0           | 25             | 100            | 54             | 16  | 1000                | 399         |
| P2209.080-16-150 | 80             | M16            | 185.0          | 35.0           | 25             | 150            | 54             | 16  | 1000                | 464         |
| P2209.080-16-175 | 80             | M16            | 235.0          | 35.0           | 25             | 200            | 54             | 16  | 1000                | 527         |
| P2209.080-20-075 | 80             | M20            | 111.0          | 36.0           | 25             | 75             | 54             | 20  | 1000                | 430         |
| P2209.080-20-100 | 80             | M20            | 136.0          | 36.0           | 25             | 100            | 54             | 20  | 1000                | 480         |
| P2209.080-20-150 | 80             | M20            | 186.0          | 36.0           | 25             | 150            | 54             | 20  | 1000                | 582         |
| P2209.080-20-200 | 80             | M20            | 236.0          | 36.0           | 25             | 200            | 54             | 20  | 1000                | 683         |
| P2209.080-24-075 | 80             | M24            | 111.0          | 36.0           | 25             | 75             | 54             | 24  | 1000                | 503         |
| P2209.080-24-100 | 80             | M24            | 136.0          | 36.0           | 25             | 100            | 54             | 24  | 1000                | 576         |
| P2209.080-24-150 | 80             | M24            | 186.0          | 36.0           | 25             | 150            | 54             | 24  | 1500                | 721         |
| P2209.080-24-200 | 80             | M24            | 236.0          | 36.0           | 25             | 200            | 54             | 24  | 1500                | 867         |
| P2209.100-16-075 | 100            | M16            | 112.5          | 37.5           | 28             | 75             | 69             | 16  | 1500                | 505         |
| P2209.100-16-100 | 100            | M16            | 137.5          | 37.5           | 28             | 100            | 69             | 16  | 1500                | 537         |
| P2209.100-16-150 | 100            | M16            | 187.5          | 37.5           | 28             | 150            | 69             | 16  | 1500                | 602         |
| P2209.100-16-200 | 100            | M16            | 237.5          | 37.5           | 28             | 200            | 69             | 16  | 1500                | 665         |
| P2209.100-20-075 | 100            | M20            | 113.5          | 38.5           | 28             | 75             | 69             | 20  | 1500                | 568         |
| P2209.100-20-100 | 100            | M20            | 138.5          | 38.5           | 28             | 100            | 69             | 20  | 1500                | 618         |
| P2209.100-20-150 | 100            | M20            | 188.5          | 38.5           | 28             | 150            | 69             | 20  | 1500                | 720         |
| P2209.100-20-200 | 100            | M20            | 238.5          | 38.5           | 28             | 200            | 69             | 20  | 1500                | 821         |
| P2209.100-20-250 | 100            | M20            | 288.5          | 38.5           | 28             | 250            | 69             | 20  | 1500                | 924         |
| P2209.100-24-100 | 100            | M24            | 138.5          | 38.5           | 28             | 100            | 69             | 24  | 1500                | 641         |
| P2209.100-24-150 | 100            | M24            | 188.5          | 38.5           | 28             | 150            | 69             | 24  | 1500                | 714         |



| Order No.        | d <sub>1</sub> | d <sub>2</sub> | h <sub>1</sub> | h <sub>2</sub> | h <sub>3</sub> | l <sub>1</sub> | l <sub>2</sub> | A/F | Load<br>kgf<br>max. | Weight<br>g |
|------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----|---------------------|-------------|
| P2209.100-24-200 | 100            | M24            | 238.5          | 38.5           | 28             | 200            | 69             | 24  | 1500                | 859         |
| P2209.100-24-250 | 100            | M24            | 288.5          | 38.5           | 28             | 250            | 69             | 24  | 1500                | 1005        |
| P2209.100-30-100 | 100            | M30            | 139.5          | 39.5           | 28             | 100            | 69             | 30  | 1500                | 906         |
| P2209.100-30-150 | 100            | M30            | 189.5          | 39.5           | 28             | 150            | 69             | 30  | 1500                | 1139        |
| P2209.100-30-200 | 100            | M30            | 239.5          | 39.5           | 28             | 200            | 69             | 30  | 1500                | 1363        |
| P2209.100-30-250 | 100            | M30            | 289.5          | 39.5           | 28             | 250            | 69             | 30  | 1500                | 1593        |



All levelling feet can be produced with the following fixing types:



### Thread versions

Metric thread - coarse pitch (standard)  
Metric thread - fine pitch  
Thread gas 55°  
Imperial thread Unc  
Whitworth thread

\* For non-standard threads a minimum order will apply.

Levelling Feet from Automation Components

LEVELLING FEET