



R3449

CLEVIS JOINTS & CLIPS

Material

Stainless steel (A2, DIN 1,4301).

Technical Notes

To DIN 94 (equivalent to ISO 1234).

Cotter pins require a loose fit, and as a result the metric versions can also be for inch sizes.

Tips

Used with clevis pins as denoted in product table, with clevis joints R3402 and R3403 and washer R3458.

Order No.	d ₁ nom.	d ₁ min.	d ₁ max.	d ₂ min.	d ₂ max.	l ₁	l ₂	l ₃	For use with clevis pin
R3449.01.0-10	1.0	0.8	0.9	0.8	1.6	10	1.6	3	R3456.004-005
R3449.01.6-18	1.6	1.3	1.4	1.25	2.5	18	2.5	3.2	R3456.006
R3449.02.0-18	2.0	1.7	1.8	1.25	2.5	18	1.25	2.5	R3456.008
R3449.03.2-22	3.2	2.7	2.9	1.6	3.2	22	3.2	6.4	R3456.010
R3449.04-28	4.0	3.5	3.7	2.0	4.0	28	4	8	R3456.012-016
R3449.05-50	5.0	4.4	4.6	2.0	4.0	50	4	10	R3456.020
R3449.06.3-71	6.3	5.7	5.9	2.0	4.0	71	4	12.6	R3456.025