




Stainless DMG Ball and Socket Joint

Ball & Socket Joints



R3532

BALL & SOCKET JOINTS

Material

Stainless steel (AISI 303).

Technical Notes

The swaging of the body produces a perma-

nent assembly and the fitted sealing cap helps resist dirt ingress.

The hexagon form of studs facilitates assembly.

Tips

Standard thread is right hand thread.

Order No.	Thread hand	d ₁	d ₂	l ₁	l ₂	h ₁	h ₂	l ₃	A/F
R3532.R006	Right	M 6	11.13	24.61	30.96	14.30	11.91	12.70	9.53
R3532.R008	Right	M 8	12.70	28.58	35.71	17.48	13.49	14.30	11.13
R3532.R010	Right	M10	15.88	34.93	42.88	22.23	17.48	19.05	12.70
R3532.R012	Right	M12	19.05	49.23	60.33	28.58	22.23	25.40	15.88
R3532.L006	Left	M 6	11.13	24.61	30.96	14.30	11.91	12.70	9.53
R3532.L008	Left	M 8	12.70	28.58	35.71	17.48	13.49	14.30	11.13
R3532.L010	Left	M10	15.88	34.93	42.88	22.23	17.48	19.05	12.70
R3532.L012	Left	M12	19.05	49.23	60.33	28.58	22.23	25.40	15.88

