





Male DMG Ball and Socket Joints

Ball & Socket Joints



R3539

BALL & SOCKET JOINTS

Material

Low carbon steel (1018), yellow zinc plated.

Technical Notes

The swaging of the body produces a perma-

nent assembly and the fitted sealing cap helps resist dirt ingress. The hexagon form of studs facilitates assembly.

Tips

Standard thread is right hand thread.

Order No.	Thread hand	d ₁	d ₂	l ₁	l ₂	h ₁	h ₂	h ₃	l ₃	A/F
R3539.R005	Right	M 5	4.37	22.23	27.00	11.13	11.13	9.53	12.04	7.95
R3539.R006	Right	M 6	4.90	24.61	30.96	14.30	11.91	11.13	12.85	9.53
R3539.R008	Right	M 8	5.89	28.58	35.71	17.48	13.49	12.70	16.03	11.13
R3539.R010	Right	M10	7.54	34.93	42.88	22.23	17.48	15.88	19.05	12.70
R3539.R012	Right	M12	10.59	49.23	60.33	28.58	22.23	19.05	25.40	15.88
R3539.L005	Left	M 5	4.37	22.23	27.00	11.13	11.13	9.53	12.04	7.95
R3539.L006	Left	M 6	4.90	24.61	30.96	14.30	11.91	11.13	12.85	9.53
R3539.L008	Left	M 8	5.89	28.58	35.71	17.48	13.49	12.70	16.03	11.13
R3539.L010	Left	M10	7.54	34.93	42.88	22.23	17.48	15.88	19.05	12.70
R3539.L012	Left	M12	10.59	49.23	60.33	28.58	22.23	19.05	25.40	15.88