





Oldham Coupling with Black Polyacetel (POM) Insert

Flexible Couplings



R3056

FLEXIBLE COUPLINGS

Material

Mainframe: Anodized aluminium AL7075.
Insert: Black polyacetel (POM)

Technical Notes

Operating temperature: -20° - 80°C.
Offset of angular, parallel or axial devia-

tion are individual allowed value,
so couple reasons of axial oddset appea-
ring at same time would reduce unit allo-
wable value.

Select bigger lock torque of clamping
screw than listen values on catalogues

when shaft diameter is too small.

List torque tightness values are only for
general standard.

Available options for key way per inner
diameter is bigger than 6mm.

Order No.	d ₁ & d ₂	d ₃	d ₄	l ₁	l ₂	l ₃	w	Clamping screw lock torque Nm	Clamping screw d ₅
R3056.A-14	14	22.5	44	46	7.5	15	14.5	8.4	M 5
R3056.A-15	15	22.5	44	46	7.5	15	14.5	8.4	M 5
R3056.A-16	16	22.5	44	46	7.5	15	14.5	8.4	M 5
R3056.A-18	18	22.5	44	46	7.5	15	14.5	8.4	M 5
R3056.A-20	20	22.5	44	46	7.5	15	14.5	8.4	M 5
R3056.B-18	18	28	55	57	9.5	19	17	14.4	M 6
R3056.B-20	20	28	55	57	9.5	19	17	14.4	M 6
R3056.B-22	22	28	55	57	9.5	19	17	14.4	M 6
R3056.B-25	25	28	55	57	9.5	19	17	14.4	M 6
R3056.C-22	22	39	70	77	12.5	25	24	30.0	M 8
R3056.C-25	25	39	70	77	12.5	25	24	30.0	M 8
R3056.C-28	28	39	70	77	12.5	25	24	30.0	M 8
R3056.C-30	30	39	70	77	12.5	25	24	30.0	M 8
R3056.C-35	35	39	70	77	12.5	25	24	30.0	M 8

