



R3540

BALL & SOCKET JOINTS

Material

Steel, (silver zinc plated). Brake piece technopolymer (polyamide PA).

Technical Notes

The clamping nut can be set to give a

required thrust on the Belleville spring washers, in order to increase resistance to the movement of the ball stud, the spring washers act as safety washers for the

screws.

Once the max. thrust to the spring washers is reached the ball stud is firmly fixed in position.

Order No.	Type	d ₁	l ₁	d ₂	d ₃	l ₂	l ₃	l ₄	l ₅	l ₆	A/F ₁	A/F ₂
R3540.MF008	MF	M8	12	11	19	10	19.5	18.5	15	-	17	9
R3540.MF010	MF	M10	15	13	21	12	23.5	21.5	17	-	19	11
R3540.MM008	MM	M8	12	11	19	-	19.5	18.5	15	-	17	9
R3540.MM010	MM	M10	15	13	21	-	23.5	21.5	17	-	19	11
R3540.FF008	FF	M8	-	11	19	10	19.5	18.5	15	-	17	9
R3540.FF010	FF	M10	-	13	21	12	23.5	21.5	17	-	19	11
R3540.FM008	FM	M8	12	11	19	-	19.5	18.5	15	18.5	17	9
R3540.FM010	FM	M10	15	13	21	-	23.5	21.5	17	20.5	19	11