




Imperial Male Rod End with Stud with Nylon bearing race

Rod Ends



R3617.i

ROD ENDS

Material

Housing and Stud: Yellow zinc plated steel.
Ball: Zinc plated, surface hardened steel.

forced nylon bearing race.

Female thread, Maintenance free, yellow zinc is not RoHS Compliant.

end studs are all Right hand threads.

Technical Notes

Features an injection molded, fibre rein-

Tips

Standard thread is Right hand thread, rod

Order No.	Thread hand	d ₁	d ₂	l ₁	w ₁	d ₃	d ₄	l ₂	l ₃	l ₄	l ₅	w ₂	A/F	a _o
R3617.I250	Right	10-32	10-32	1.562	0.375	0.750	0.304	1.000	0.469	0.562	0.125	0.281	0.375	25
R3617.I313	Right	5/16-24	5/16-24	1.875	0.437	0.875	0.356	1.250	0.531	0.687	0.125	0.344	0.437	25
R3617.I375	Right	3/8-24	3/8-24	2.000	0.500	1.090	0.424	1.250	0.644	0.906	0.187	0.406	0.500	25
R3617.I500	Right	1/2-20	1/2-20	2.437	0.625	1.380	0.564	1.500	0.875	1.125	0.250	0.500	0.625	25
R3617.I625	Right	5/8-18	5/8-18	2.625	0.750	1.500	0.622	1.625	1.000	1.125	0.375	0.562	0.750	25
R3617.I750	Right	3/4-16	3/4-16	2.875	0.875	1.750	0.747	1.750	1.187	1.812	0.375	0.687	1.000	25
R3617.IL250	Left	10-32	10-32	1.562	0.375	0.750	0.304	1.000	0.469	0.562	0.125	0.281	0.375	25
R3617.IL313	Left	5/16-24	5/16-24	1.875	0.437	0.875	0.356	1.250	0.531	0.687	0.125	0.344	0.437	25
R3617.IL375	Left	3/8-24	3/8-24	2.000	0.500	1.090	0.424	1.250	0.644	0.906	0.187	0.406	0.500	25
R3617.IL500	Left	1/2-20	1/2-20	2.437	0.625	1.380	0.564	1.500	0.875	1.125	0.250	0.500	0.625	25

